Product Specifications





EWP77-71W

EWP77, HELIAX® Premium Elliptical Waveguide, 7.125-8.5 GHz, black PE jacket

Construction Materials

Jacket Material	P	Е
-----------------	---	---

Conductor Material Corrugated copper

Jacket Color Black

Dimensions

Cable Volume	585.0 L/km 6.3 ft³/kft
Cable Weight	0.67 kg/m 0.45 lb/ft
Diameter Over Jacket (E Plane)	43.60 mm 1.72 in
Diameter Over Jacket (H Plane)	25.40 mm 1.00 in

Electrical Specifications

Operating Frequency Band	7.125 – 8.5 GHz		
eTE11 Mode Cutoff	4.720 GHz		

Group Delay 128 ns/100 ft @ 7.800 GHz 419 ns/100 m @ 7.800 GHz

Environmental Specifications

Installation Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)

General Specifications

Brand HELIAX®

Mechanical Specifications

Maximum Twist	3.00 °/m	1.	00 °/ft
Minimum Bend Radius, Multiple Bends (E Plane)	230.00 mm		9.00 in
Minimum Bend Radius, Multiple Bends (H Plane)	635.00 mm		25.00 in
Minimum Bend Radius, Single Bend (E Plane)	180.00 mm		7.00 in
Minimum Bend Radius, Single Bend (H Plane)	510.00 mm	1	20.00 in

Note

Performance Note Values typical, unless otherwise stated

Standard Conditions

Attenuation, Ambient Temperature	24 °C	75 °F
Average Power, Ambient Temperature	40 °C	104 °F
Average Power, Temperature Rise	42 °C	76 °F

Product Specifications



EWP77-71W

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
7.125-8.5 GHz	1.06	30.70

^{*} VSWR/Return Loss indicated is for lengths up to 300 ft (91.4 m)

Attenuation

Frequency (GHz)	Attenuation (dB/100 ft)	Attenuation (dB/100 m)	Average Power (kW)	Group Velocity %
7.1	1.907	6.258	3.122	74.9
7.3	1.863	6.113	3.196	76.4
7.5	1.825	5.988	3.263	77.8
7.7	1.792	5.88	3.323	79.1
7.9	1.764	5.786	3.377	80.3
8.1	1.739	5.705	3.425	81.4
8.3	1.717	5.634	3.468	82.4

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

ISO 9001:2008

Classification

Compliant

Below Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system





^{*} VSWR/Return Loss is guaranteed for factory-fit and typical for field-fit assemblies

^{*} Custom length performance: Call 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative