

1-599172-2

**Outside Plant Fiber Optic Cable, 8-fiber, OM4, ULSZH, loose tube, gel-filled, 1000 m**

## Body Features

Cable Color	Aqua
Cable Construction	1 x 12
Bend Radius (Installation)	228.60 mm   9.00 in
Bend Radius (Long Term)	175.26 mm   6.90 in
Tensile Strength (Installation)	2001.70 N   450.00 lbf
Tensile Strength (Long Term)	750.00 N   168.61 lbf
Weight (Nominal)	94.0 kg/km

## Configuration Features

Number of Fibers	12
------------------	----

## Dimensions

Length	999.99 m   3280.80 ft
Outside Diameter	9.00 mm   0.35 in

## Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

## Operation/Application

Environment	Outdoor
-------------	---------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Armoring	Non-Metallic
Fiber Type	OM4
Cable Type	Fiber Optic
Fiber Cable Buffering	Loose tube, gel-filled
Fiber Diameter	50/125 $\mu$ m
Fiber Specification	IEC 60794-1
Product Type	Cable
System	AMP NETCONNECT

## Signal Characteristics

Attenuation, maximum (1300nm)	1.00 dB/km
Attenuation, maximum (850nm)	3.50 dB/km

## Usage Conditions

Installation Temperature Range	-5 – 50 °C
--------------------------------	------------

1-599172-2

Operating Temperature Range    -20 – 70 °C   |   -4 – 158 °F  
Storage Temperature Range       -20 – 70 °C

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant