



CT-2920/CCP • CT-2920/CCPINT • CT-2920/CCPUK
• CT-2920/CCPAUS • CT-2920/CCPTO
MULTI-USE (CRIMP • CUT • PUNCH) TOOL

This tool meets requirements of Safety for Hand Heldheld, Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No 60745-1. Tool is listed under CSA file number 268531.

NOTES, UNLESS OTHERWISE SPECIFIED:

The CT-2920/CCP, CT-2920/CCPINT, CT-2920/CCPUK, CT-2920/CCPAUS and CT-2920/CCPTO Battery Operated Multi-Use Tools are designed to crimp, cut and punch:

- Crimps Panduit Copper and Aluminum compression connectors using Panduit Crimping Dies. Go to www.panduit.com for more information.
- Cuts Aluminum and Copper code conductor cable up to 1.57" [40mm].
- Cuts Aluminum and Mild Steel Threaded Rod; M5 to M12, and 1/4 to 1/2 UNC Thread.
- Punch capacity is 5-5/8" (144 mm) diameter round hole in 10 gauge (3.41 mm) mild steel using standard Greenlee punches and Panduit punch drive adapter.

The CT-2920/CCP, CT-2920/CCPINT, CT-2920/CCPUK and CT-2920/CCPAUS Tools include:

Qty.	Description / Item			
1	Battery Operated Hydraulic Multi-Use (Crimp, Cut, Punch) Tool			
2	Rechargeable Battery (Makita Lithium-Ion 18VDC, 3Ah)			
1	/CCP	/CCPINT	/CCPUK	/CCPAUS
	Plug Type A (North America)	Plug Type C (International)	Plug Type G (UK)	Plug Type I (Australia)
	Makita Battery Charger – Regional (reference images above for regional plug type)			
1	Plastic Tool Case with Die and Cutting Blade Storage			
1	Tool Carrying Strap			
1	Set of Panduit "UA12TKL" Die Adapters			



The CT-2920/CCPTO Tool includes:

Qty.	Description / Item
1	Battery Operated Hydraulic Multi-Use (Crimp, Cut, Punch) Tool
1	Set of Panduit "UA12TKL" Die Adapters

Technical Information:

Tool Weight (including battery)	14.3 lbs. (6.5 kg)
Dimensions (including battery) are for reference only.	16.8" L x 13.1" H x 3.0" W [426 L x 333 H x 75 W] mm
Crimping Force	12 tons (108 kN)

Tools are to be used with Panduit crimp dies, cable cutters, threaded rod cutters, punch driver adapters, and are sold separately. Go to www.panduit.com for more information. A copy of the operation manual and accessory information can be found at www.panduit.com.

							CT-2920/CCP, CT-2920/CCPINT, CT-2920/CCPUK, CT-2920/CCPAUS and CT-2920/CCPTO CUSTOMER DRAWING					
							ITEM REVISION NAME:					
							00084SLA_DC/00					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:				MATERIAL: -----	
							(.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---					
00	7-25-16	BAK	ACC	JADE	DRAWING RELEASED	010819	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 00084SLA_DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BAK	DATE: 7-21-16	CHK ACC	SCALE NONE	SHT 1 OF 1	SIZE B