

2



1




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
Q1N1B1EOA30AHA0	6.97kg (15.4lb)

NOTES:  
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 AND (6) C-19, NETWORKED 208V / 20A / SINGLE PHASE PDU


PART NO. Q1N1B1EOA30AHA0  
COLOR BLACK

2. ACCESSORY COMPONENTS:  
(1) QUICK-START GUIDE
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
4. CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION OR ON-UNIT DISPLAY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 3.3 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




TOP VIEW


SIDE VIEW



PLUG  
20 AMP, 250V  
STRAIGHT BLADE  
NEMA 6-20P



TWENTY-FOUR (24)  
RECEPTACLES  
15 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13



SIX (6)  
RECEPTACLES  
20 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

00A	03/25/14	PJST	MRWA	EDM	RELEASED TO PRODUCTION	12V092BZ-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
Q1N1B1EOA30AHA0			
CUSTOMER DRAWING			
ITEM REVISION NAME		12V092BZ/00	
DATASET FILE NAME		12V092BZ_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	METRIC - MILLIMETER	ANGLE	
X.X +/- 0.03	X. +/- 0.8	+/- 1°	
X.XX +/- 0.018	X.X +/- 0.46		
X.XXX +/- 0.007	X.XX +/- 0.18		
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY PJST		12V092BZ - DC	
DATE 03/26/14	CHK MRWA	SCALE 1:8	SIZE B
SHT 1 OF 1			