

## Product information ACA31

Industrial Ethernet:System Accessories:Adapter c	able:ACA31
https://e-catalog.beldensolutions.com:443/link/57078-24455-24544-24546-253498/en/conf/uistate	
Name	ACA31
	The second s
	Ante configuration adapter CD and with F10MD extended temperature many annual to different versions of configuration data and exception ofference form
	Auto-configuration adapter, SD card with 512MB, extended temperature range, saves two different versions of configuration data and operating software from the consected with the appleae managed withher to be easily completed and withher the construction of the const
Delivery informations	the connected switch. It enables managed switched to be easily comissioned and quickly replaced.
Availability	available
Product description	uvundute
Description	Auto-configuration adapter, SD card with 512MB, extended temperature range, saves two different versions of configuration data and operating software from
•	the connected switch. It enables managed switched to be easily comissioned and quickly replaced.
Туре	ACA31
Order No.	942 074-001
Power requirements	
Operating voltage	via the SD switch interface
Service	
Diagnostics	writing to ACA, reading from ACA, writing/reading not OK (display using LEDs on the switch)
Configuration	via SD switch interface
Ambient conditions	
Operating temperature	-40 °C 85 °C
Storage/transport temperature	-40 °C 85 °C
Relative humidity (non-condensing)	10 % 95 %
Mechanical construction	
Dimensions (W x H x D)	32 mm x 24 mm x 2,1 mm
Mounting	plug-in module
Weight	59
Protection class	IP20
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 g, 10 Hz - 150 Hz, 30 cycles
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m
EMC emitted immunity	
EN 55022	EN 55022
Scope of delivery and accessories	
Scope of delivery	device, operating manual

For more information please contact: Hirschmann Automation and Control GmbH Stuttgarter Strasse 45-51 72654 Neckartenzlingen Germany

www.beldensolutions.com





Phone: +49 7127/14-1809 E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.

