

111-01128



Article Number: 111-01128

High Temp Tie, 15.35" Long, 50lb Tensile Strength, PA66HIRHSUV, Black, 1000/pkg



Base Data

Local Order Number	111-01128
Type	T50L
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• High impact, heat and UV stabilized cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.• Inside serrations allow for strong hold on cables and wire bundles.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton high temperature cable ties are made of specially formulated materials providing various levels of temperature resistance and performance. The cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Fixation Method (FF)	None
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Short Description	High Temp Tie, 15.35" Long, 50lb Tensile Strength, PA66HIRHSUV, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	50.0 lbs
Minimum Tensile Strength (N)	225.0 N
Length L (imperial)	15.35 "
Length L (metric)	390.0 mm
Width W (imperial)	0.18 "
Width W (metric)	4.7 mm
Bundle Diameter min (imperial)	0.06 "
Bundle Diameter min (metric)	1.5 mm
Bundle Diameter max (imperial)	4.3 "
Bundle Diameter max (metric)	110.0 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	1000
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL94 HB
Operating Temperature	-40 °F to +230 °F (-40 °C to +110 °C)
ROHS Conformity	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No