



2111571-1

AMP-TWIST Modular Patch Panel, category 6A, U/UTP, class EA, unshielded, flat, 48-port, 2U, black

Body Features

Color	Black
-------	-------

Configuration Features

Custom Configurable	No
Front Connector Type	RJ45
Number of Rear Connectors	48
Preloaded	No

Dimensions

Rack Width	482.60 mm 19.00 in
------------	----------------------

Mechanical Attachment

Mounting Style	Rack-Mount
----------------	------------

Product Type Features

Product Type	Patch Panel
System	AMP NETCONNECT AMP-TWIST
Panel Type	Patch Panel
Product Category	RJ45 Patch Panel
Rack Units	2.0
Cable Type	UTP
Performance Category	Category 6A
Shielded	No

Signal Characteristics

Ethernet Speed	10 Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------