

**3-1553415-9****Fiber Optic Cable, dualan, OFNP, 2.9 mm, OM3, aqua**

Body Features

Cable Color	Aqua
Cable Construction	1 x 2
Bend Radius (Installation)	57.00 mm 2.24 in
Bend Radius (Long Term)	29.00 mm 1.14 in
Tensile Strength (Installation)	97.86 N 22.00 lbf
Tensile Strength (Long Term)	31.14 N 7.00 lbf
Weight (Nominal)	9.0 kg/km 6.0 lb/kft

Configuration Features

Number of Fibers	2
------------------	---

Dimensions

Outside Diameter	2.90 mm 0.11 in
------------------	-------------------

Industry Standards

Flammability Rating	OFNP (Plenum) Jacket
Standards Compliance	ANSI/ICEA S-83-596 ANSI/TIA-568 ANSI/TIA/EIA-568-B.1 ANSI/TIA/EIA-568-B.2 Telcordia GR-409 Telcordia GR-409-CORE

Operation/Application

Environment	Indoor
-------------	--------

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Cable
Fiber Type	OM3
Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Tight buffer
Fiber Diameter	50/125 µm
Fiber Specification	IEC 60793-2-10 A1a.2 TIA-492AAAC
Optical Mode	Multimode
System	AMP NETCONNECT

3-1553415-9

Signal Characteristics

10GbE Transmission Distance (Min) (850nm)	300.0 m 984.3 ft
Attenuation, maximum (1300nm)	1.00 dB/km
Attenuation, maximum (850nm)	3.20 dB/km
Effective Modal Bandwidth (Min) (850nm)	2000 MHz-km
Overfilled Launch Bandwidth (Min) (1300nm)	500 MHz-km
Overfilled Launch Bandwidth (Min) (850nm)	1500 MHz-km

Usage Conditions

Installation Temperature Range	0 – 60 °C 32 – 140 °F
Operating Temperature Range	0 – 70 °C 32 – 158 °F
Storage Temperature Range	-40 – 158 °F -40 – 70 °C

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant