

559561-3

Wall Mount Patch Enclosure, 24 ports, double sided, double door, with lock and flat tie holders

Body Features

Color	Black
Enclosure Material	Steel
Finish	Enamel

Configuration Features

Port Capacity	24
Number of Doors	2
Number of Fibers	24
Patch Panel Alignment	Center
Preloaded	No

Dimensions

Enclosure Dimensions	13.5 x 15.13 x 4.1
Width	384.300 mm 15.130 in

Identification Marking

Labeled	Yes
---------	-----

Mechanical Attachment

Mount Style	Wall
-------------	------

Operation/Application

Accepts	Adapter Plates & Cassettes
Universal Connectivity Platform	No

Other

Optional Accessories	Splice Holder
----------------------	---------------

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Enclosure
System	AMP NETCONNECT
Enclosure Type	Patch
Lockable	Yes

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant