



61292-2

PICABOND® Connector, 1000 loose piece, 400 Vdc, yellow

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

Body Features

Cable Insulation Material	Air Core PIC Foam Filled PIC
Color Code	Yellow
Sealant	Gel filled

Contact Features

Contact Base Material	Phosphor bronze
Contact Plating Material	Tin

Dimensions

Wire Size (CMA)	24 – 19 AWG
-----------------	-------------

Electrical Characteristics

Voltage Rating	400 Vdc
----------------	---------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000

Product Availability

Region	Australia/New Zealand EMEA Latin America North America
--------	--

Product Type Features

Product Type	Splice
System	PICABOND
Splicing Applications	Bridge Butt Full Bridge Half-tap Straight (In-line)

Usage Conditions

Operating Temperature	-40 – 60 °C
-----------------------	-------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant