



309-60329



Article Number: 309-60329

Heat Shrink Tubing, Bulk Reel, 2:1, 1.5", 38.1/19.1 dia., Polyolefin, White, 100.0 ft/Reel

 RoHS

Base Data

Local Order Number	309-60329
Type	TFN21-38.1/19.1 WH
Color	White (WH)
Features and Benefits	<ul style="list-style-type: none"><li>• Thin, 2 to 1 shrink ratio tubing provides insulation and abrasion protection for wires and cables.</li><li>• Flammability rating of UL224 VW-1 for use in applications requiring the highest degree of flame protection (excludes clear tubing).</li><li>• Flexible-yet-durable material resists most common oils, chemicals and fluids.</li><li>• Available in a variety of diameters and colors for identifying and marking wires and cables.</li><li>• Available in mini reels, bulk reels, and sticks for small to large volume applications.</li></ul>
Product Description	TFN21 is a highly flexible thin wall heat shrink tubing with a 2 to 1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. Available in mini reels, bulk reels and sticks, for small to large volume applications.
Short Description	Heat Shrink Tubing, Bulk Reel, 2:1, 1.5", 38.1/19.1 dia., Polyolefin, White, 100.0 ft/Reel

Product Dimensions

Length L2 (Imperial)	100.0 ft
Length L2 (Metric)	30.5 m
Printable (Yes/No)	Yes
Shrink Ratio	2:1
Tensile Strength (MPa)	14 MPa
Trade Size	1-1/2 "
Variant	Thin-Wall
Volume Resistance (Ohm cm)	10 <sup>11</sup> Ω cm
Nominal Diameter (Imperial)	1-1/2 "
Nominal Diameter (Metric)	38.1 mm
Wall Thickness WT (Imperial)	0.039 "
Wall Thickness WT (Metric)	1.0 mm
Recovered Diameter d (metric)	19.1 mm
Recovered Diameter d (imperial)	0.752 "
Supplied Diameter D (imperial)	1.5 "
Supplied Diameter D (metric)	38.1 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	100 ft

Material and Specifications

---

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Dielectric Strength (Metric)	20 kV/mm
Elongation at break	6
Flammability	UL224 VW-1
Halogenfree	No
Shrink Temperature	+212 °F (+100 °C)
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
ROHS Compliant	Yes
Certification/Specification	CSA UL224 125 °C 600V VW-1
UL Recognized (US)	Yes