

SNP10GHS0C2



Article Number: 192-10100

Snapper Hose Clamps, .571"/.654" Min/Max Diameter, PA66GF13%, Black, 100/pkg

 RoHS

Base Data

| | |
|-----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Local Order Number | SNP10GHS0C2 |
| Type | SNP10 |
| Color | Black (BK) |
| Features and Benefits | <ul style="list-style-type: none">• Designed for quick, ratcheted installation and can be released and reused.• Heat stabilized material is suitable for high temperature applications. |
| Product Description | HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes. |
| Fixation Method (FF) | Plug-in mounting |
| Variant | Closed |
| Short Description | Snapper Hose Clamps, .571"/.654" Min/Max Diameter, PA66GF13%, Black, 100/pkg |

Product Dimensions

| | |
|--------------------------------|----------|
| Width W min (imperial) | 0.693 " |
| Width W min (metric) | 17.6 mm |
| Width W Max (imperial) | 1.059 " |
| Width W max (metric) | 26.9 mm |
| Width W2 (imperial) | 0.232 " |
| Width W2 (metric) | 5.89 mm |
| Bundle Diameter min (imperial) | 0.56 " |
| Bundle Diameter min (metric) | 14.5 mm |
| Bundle Diameter max (imperial) | 0.65 " |
| Bundle Diameter max (metric) | 16.6 mm |
| Diameter min. (imperial) | 0.571 " |
| Diameter min. (metric) | 14.5 mm |
| Diameter max. (imperial) | 0.654 " |
| Diameter max. (metric) | 16.61 mm |
| Nominal Diameter (imperial) | 0.63 " |
| Nominal Diameter (metric) | 16 mm |
| Wall Thickness WT (imperial) | 0.069 " |
| Wall Thickness WT (metric) | 1.8 mm |

Logistics and Packaging

| | |
|------------------|-----|
| Quantity per | bag |
| Package Quantity | 100 |

Carton Quantity 100 Pieces

Weight (Metric) 0.24 kg

Material and Specifications

Material Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)

Material Shortcut PA66GF13

Flammability UL94 HB

Operating Temperature -40 °F to +221 °F (-40 °C to +105 °C)

ROHS Conformity Yes