

General Description:



The SL-500X™ ServerLIFT is a heavy duty electric lift for servers, switches, UPS devices and other rack-mounted equipment.

The SL-500X™ ServerLIFT loads IT equipment up to 500 lbs. from the side for optimum alignment over the full range of most any standard 19" rack.



Features:

- Powered lifting with the touch of a button.
- TouchSTOP™ sensor prevents overhead damage.
- Side loading with 6" of movement to either side.
- Heavy duty platform resists sagging and twisting.
- Smart Controls for fast lifting and precise alignment.
- Dual locking stabilizer brakes.
- Compact, maneuverable design.
- Non-hydraulic electric winch easily lifts 500 lbs.



Product Dimensions	US	Metric
Unit Height (Lowered):	5 ft 9.4 in	1.76 m
Unit Height (Raised):	9 ft 4.2 in	2.85 m
Length	3 ft 8 in	1.12 m
Width	2 ft 0.5 in	0.62 m

Capacity and Weight	US	Metric
Load Capacity-Platform Center	500 lbs	226.8 kg
Load Capacity-Edge	300 lbs	136.1 kg
Total Unit Weight	428 lbs	194 kg

Working Dimensions	US	Metric
Platform Height-Extended	8 ft	2.44 m
Platform Height-Stowed	5.3 in	13.5 cm
Platform-Movement (per side)	6 in	15.2 cm
Movable Platform-Width	14.6 in	36.8 cm
Platform Length	24 in	61 cm
Total Platform Width	21 in	53 cm
Rear Caster Diameter	5 in	12.7 cm
Front Caster Diameter	4 in	10.2 cm
Caster Width	2 in	5.08 cm