

B23 111-100



Products Low Voltage Products and Systems Modular DIN Rail Products Electricity Meters for DIN Rail Electricity Meters

General Information

Extended Product Type:	B23 111-100
Product ID:	2CMA100163R1000
ABB Type Designation:	B23 111-100
EAN:	7392696001632
Catalog Description:	Active energy Cl. B;
Long Description:	Electricity meter, 3 phase, Active energy Cl. 1 & B, Approved according to: IEC 62052-11, IEC 62053-21, EN 50470-1, EN 50470-3

Additional Information

ABB Type Designation:	B23 111-100
Accuracy:	Active energy Cl. B
Communication:	Pulse output / IR port
Communication Interface:	Pulse output
Connecting Capacity Main Circuit:	1 ... 25 mm ²
Country of Origin:	Sweden (SE)
Customs Tariff Number:	90283019
Data Sheet, Technical Information:	2CMC481003C0201
Declaration of Conformity - CE:	2CMC485001D0001
Degree of Protection:	IP20
E-nummer:	0900036
EAN:	7392696001632
ETIM 4:	EC001506 - Electronic kilowatt-hour meter
ETIM 5:	EC001506 - Kilowatt-hour meter
ETIM 6:	EC001506 - Kilowatt-hour meter
Enclosure Material:	Plastic
Environmental Information:	2CMC485003D0001
Frequency (f):	50/60 Hz
Function:	Electricity meter
Gross Weight:	0.39 kg
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC485014M0201
Invoice Description:	kWh meter#B23 111-100
Meter Type:	Direct connected
Minimum Order Quantity:	1 piece
Mounting Type:	DIN rail
Number of Phases:	3
Object Classification Code:	P
Package Level 1 EAN:	7392696001632
Package Level 1 Gross Weight:	0.39 kg
Package Level 1 Height:	68 mm
Package Level 1 Length:	94 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	100 mm
Product Main Type:	B23
Product Name:	Electricity Meter

