



L4A-PDMDR-1M-3GSH

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 1 m

OBSOLETE

This product was discontinued on: December 31, 2010

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	1.000 m 3.281 ft
Specification Sheet Revision Level	A

Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-30.00 dB

Jumper Assembly Sample Label

Batch 0123456789 | **Manufacturing Date** (two digit year and week) US22 1240 | **Product Revision** /A
Manufacturing Plant US22 | **Part Number** F4-DMDM-2M-D
 2 M (6.562 FT)
 SUREFLEX ASSEMBLY
 U.S. PATENT 5802710
 Product of UNITED STATES | **Serial Number** 12US220001242

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.08	28.00
1700–2200 MHz	1.10	26.40

Regulatory Compliance/Certifications

L4A-PDMDR-1M-3GSH

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

CX-10D-SA — HELIAX® Low Density Foam Coaxial Cable, corrugated copper, black PE jacket, special marking "SWCC SHOWA CX-10D-SA ANDREW HELIAX® 1/2" LDF4-50A"

LDF4-50A-2T — LDF4-50A-2T, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

12L450 — 1/2", HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket