

# E 92/32 PV



Products Low Voltage Products and Systems Modular DIN Rail Products Modular DIN Rail Components MDRCs Fuse Holders

## General Information

<b>Extended Product Type:</b>	E 92/32 PV
<b>Product ID:</b>	2CSM204703R1801
<b>EAN:</b>	8012542047032
<b>Catalog Description:</b>	E 92/32 PV Fuse holder
<b>Long Description:</b>	E 92/32 PV is a fuseholder for overcurrent and short circuit protection in PV applications. No blown fuse indicator.

## Additional Information

<b>Country of Origin:</b>	Romania (RO)
<b>Customs Tariff Number:</b>	85361010
<b>Data Sheet, Technical Information:</b>	2CSC444002B0204
<b>Declaration of Conformity - CE:</b>	2CSC444003D2701
<b>Dimensions:</b>	1 module
<b>E-nummer:</b>	2318054
<b>EAN:</b>	8012542047032
<b>ETIM 4:</b>	EC000036 - Miniature fuse holder
<b>ETIM 5:</b>	EC000036 - Miniature fuse holder
<b>ETIM 6:</b>	EC000036 - Miniature fuse holder
<b>Environmental Information:</b>	See RoHS Information
<b>Fuse Size:</b>	Cylindrical PV 10,3x38
<b>Instructions and Manuals:</b>	On the product's body
<b>Invoice Description:</b>	E 92/32 PV Fuse holder
<b>Minimum Order Quantity:</b>	1 piece
<b>Number of Poles:</b>	2
<b>Number of Protected Poles:</b>	2
<b>Object Classification Code:</b>	F
<b>Package Level 1 EAN:</b>	8012542047049
<b>Package Level 1 Gross Weight:</b>	0.369 kg
<b>Package Level 1 Height:</b>	0.085 m
<b>Package Level 1 Length:</b>	0.064 m
<b>Package Level 1 Units:</b>	3 piece
<b>Package Level 1 Width:</b>	0.105 m
<b>Power Loss:</b>	at Rated Operating Conditions per Pole 3 W
<b>Product Main Type:</b>	E 90 PV
<b>Product Name:</b>	Fuse disconnecter
<b>Product Net Depth:</b>	0.064 m
<b>Product Net Height:</b>	0.085 m
<b>Product Net Weight:</b>	0.122 kg
<b>Product Net Width:</b>	0.035 m
<b>Rated Current (I<sub>n</sub>):</b>	32 A
<b>Rated Operational Voltage:</b>	1000 V DC
<b>Rated Primary Current (I<sub>pn</sub>):</b>	32 A
<b>RoHS Date:</b>	1/1/2014
<b>RoHS Information:</b>	2CSC444011K2701
<b>RoHS Status:</b>	Following EU Directive 2011/65/EC
<b>Selling Unit of Measure:</b>	piece
<b>Voltage Range:</b>	1000 V DC

