

General Information

Extended Product Type:	S203-C25
Product ID:	2CDS253001R0254
EAN:	4016779468206
Catalog Description:	Miniature Circuit Breaker - S200 - 3P - C
Long Description:	System pro M compact S200 miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200 comply with IEC/EN 60898-1, IEC/EN 60947-2, UL 1077 and CSA 22.2 No. 235, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200 to save 50% space.

Additional Information

Actuator Material:	Insulation Group II, Black, Sealable
Actuator Type:	Insulation group II, black, sealable
Ambient Air Temperature:	Operation -25 ... +55 °C Storage -40 ... +70 °C
Built-In Depth (t₂):	69 mm
Connecting Capacity:	Busbar 10 / 10 mm ² Flexible with Ferrule 0.75 ... 25 mm ² Flexible 0.75 ... 25 mm ² Rigid 0.75 ... 35 mm ² Stranded 0.75 ... 35 mm ²
Connecting Capacity UL/CSA:	Busbar 18-8 AWG Conductor 18-4 AWG
Contact Position Indication:	Red ON / Green OFF
Country of Origin:	Germany (DE)
Customs Tariff Number:	85362010
Data Sheet, Technical Information:	2CDC002157D0102
Declaration of Conformity - CE:	2CDK403001D0604
Degree of Protection:	IP20
Dielectric Test Voltage:	50 / 60 Hz, 1 min: 2 kV
E-number:	2100604
EAN:	4016779468206
EPLAN Catalog Tree:	Electrical engineering / Protection devices / General
EPLAN Function Definition:	Circuit breaker / Triple circuit breaker / Triple circuit breaker 1_2_3_4_5_6
EPLAN Macro:	9AKK106713A8194
ETIM 4:	EC000042 - Miniature circuit breaker (MCB)
ETIM 5:	EC000042 - Miniature circuit breaker (MCB)
ETIM 6:	EC000042 - Miniature circuit breaker (MCB)
Electrical Endurance:	20000 AC cycle
Energy Limiting Class:	3
Environmental Conditions:	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Environmental Information:	2CDK400030D0201
Frequency (f):	50 Hz
Housing Material:	Insulation Group II RAI 7035

Accessories:	Installation Group II, Type 1000
Industrial IT Certification Level:	0
Installation Size:	acc. to DIN 43880 1
Instructions and Manuals:	2CSC400002D0208
Interrupting Rating acc. to UL1077:	(110 V DC) 10 kA (277 V AC) 6 kA (480Y / 277 V AC) 6 kA
Invoice Description:	S203-C 25 Mini Circuit Breaker C-Char.,6kA,25A,3P
Maximum Operating Voltage UL/CSA:	110 V DC 480Y/277 V AC
Mechanical Endurance:	20000 cycle
Minimum Order Quantity:	1 piece
Mounting Position:	Any
Mounting on DIN Rail:	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Number of Poles:	3
Number of Protected Poles:	3
Object Classification Code:	F
Operational Voltage:	Maximum (Incl. Tolerance) 440 V AC Maximum 440 V AC Minimum 12 V AC Minimum 12 V DC
Overvoltage Category:	III
Package Level 1 EAN:	4016779609272
Package Level 1 Gross Weight:	0.4 kg
Package Level 1 Height:	80 mm
Package Level 1 Length:	58 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	92 mm
Package Level 2 EAN:	4016779973267
Package Level 2 Gross Weight:	13.36 kg
Package Level 2 Height:	210 mm
Package Level 2 Length:	395 mm
Package Level 2 Units:	36 piece
Package Level 2 Width:	275 mm
Pole Net Weight:	0.115 kg
Pollution Degree:	3
Power Loss:	9.6 W at Rated Operating Conditions per Pole 3.2 W
Power Supply Connection:	Arbitrary
Product Main Type:	S200
Product Name:	Miniature Circuit Breaker
Product Net Depth:	69 mm
Product Net Height:	88 mm
Product Net Weight:	0.375 kg
Product Net Width:	52.5 mm
Product Range:	S200
Rated Current (I _n):	25 A
Rated Frequency (f):	50 Hz 60 Hz
Rated Impulse Withstand Voltage (U _{imp}):	4 kV (6.2 kV @ sea level)

5.0 kV @ 2000 m)

Rated Insulation Voltage (U _i):	acc. to IEC/EN 60664-1 440 V
Rated Operational Voltage:	acc. to IEC 60898-1 400 V AC acc. to IEC 60947-2 440 V AC
Rated Service Short-Circuit Breaking Capacity (I _{cs}):	(230 V AC) 15 kA
Rated Short-Circuit Capacity (I _{cn}):	(400 V AC) 6 kA
Rated Ultimate Short-Circuit Breaking Capacity (I _{cu}):	(230 V AC) 20 kA (440 V AC) 10 kA
Rated Voltage (U _r):	400 V AC
Recommended Screw Driver:	Pozidriv 2
Reference Ambient Air Temperature:	30 °C
Remarks:	IP40 in enclosure with cover
Resistance to Shock acc. to IEC 60068-2-27:	25g / 2 shocks / 13 ms
Resistance to Vibrations acc. to IEC 60068-2-6:	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
RoHS Date:	0335
RoHS Information:	2CDK400003K0201
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Screw Terminal Type:	Failsafe Bi-directional Cylinder-lift Terminal
Selling Unit of Measure:	piece
Short Description:	S203-C 25 Mini Circuit Breaker
Standards:	IEC/EN 60898-1 IEC/EN 60947-2 UL 1077
Terminal Type:	Screw Terminals
Tightening Torque:	2.8 N·m
Tightening Torque UL/CSA:	25 in·lb
Tripping Characteristic:	C
UNSPSC:	39121614
Width in Number of Modular Spacings:	3
eClass:	7.0 27141901
Accessories Available:	Yes
Actuator Marking:	I / O
EPLAN Graphical Macro:	9AKK106713A8196

Accessories

32 Products

Filter

Identifier	Description	Type	Qty	Unit Of Measure
2CCA880100R0001	CMS-100PS	CMS-100PS	1	piece
2CCA880101R0001	CMS-101PS	CMS-101PS	1	piece
2CCA880102R0001	CMS-102PS	CMS-102PS	1	piece
2CDS200909R0001	S2C-A1 - Shunt Trip	S2C-A1	1	piece
2CDS200909R0002	S2C-A2 - Shunt Trip	S2C-A2	1	piece
2CDS200912R0001	S2C-H6R - Auxiliary Contact	S2C-H6R	1	piece
2CDS200918R0001	S2C-NT - Hand Operated Neutral	S2C-NT	1	piece
2CDS200922R0001	S2C-S/H6R - Signal / Auxiliary Contact	S2C-S/H6R	1	piece

2CDS200936R0001	S2C-SH11L - Signal / Auxiliary Contact	S2C-SH11L	1	piece
Identifier	Description	Type	Qty	Unit Of Measure
2CDS200936R0001	S2C-H11L - Auxiliary Contact	S2C-H11L	1	piece
2CDS200936R0002	S2C-H20L - Auxiliary Contact	S2C-H20L	1	piece
2CDS200936R0003	S2C-H02L - Auxiliary Contact	S2C-H02L	1	piece
2CDS200946R0001	S2C-H6-11R - Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0002	S2C-H6-20R - Auxiliary Contact	S2C-H6-20R	1	piece
2CDS200946R0003	S2C-H6-02R - Auxiliary Contact	S2C-H6-02R	1	piece
2CDS200970R0001	S2C-H01 - Auxiliary Contact	S2C-H01	1	piece
2CDS200970R0002	S2C-H10 - Auxiliary Contact	S2C-H10	1	piece
2CSS200911R0001	S2C-UA 12 DC - Undervoltage release	S2C-UA 12 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC - Undervoltage release	S2C-UA 24 AC	1	piece
2CSS200911R0003	S2C-UA 48 AC - Undervoltage release	S2C-UA 48 AC	1	piece
2CSS200911R0004	S2C-UA 110 AC - Undervoltage release	S2C-UA 110 AC	1	piece
2CSS200911R0005	S2C-UA 230 AC - Undervoltage release	S2C-UA 230 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC - Undervoltage release	S2C-UA 400 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC - Undervoltage release	S2C-UA 24 DC	1	piece
2CSS200911R0008	S2C-UA 48 DC - Undervoltage release	S2C-UA 48 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC - Undervoltage release	S2C-UA 110 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC - Undervoltage release	S2C-UA 230 DC	1	piece
2CSS200998R0001	S2C-BP - Mechanical tripping device	S2C-BP	1	piece
2CSS200999R0001	S2C-EST - Plug-in base	S2C-EST	1	piece
2CSS201997R0013	S2C-CM1 - Motor operating device	S2C-CM1	1	piece
2CSS203997R0013	S2C-CM2/3 - Motor operating device	S2C-CM2/3	1	piece
2CSS204997R0013	S2C-CM4 - Motor operating device	S2C-CM4	1	piece
GHS2001901R0003	S2C-DH - Mechanical Accessories	S2C-DH	1	piece

