



SMALL-CAPKIT


Female End Cap Assembly for 4.3-10 series and 4.1-9.5 Din, work torque 5-8N/M.

General Specifications

Brand

HELIAX®

Outline Drawing



Mechanical Specifications

Coupling Nut Proof Torque	8.00 N-m 5.90 ft lb
---------------------------	-----------------------

Dimensions

Diameter	22.00 mm 0.87 in
Length	13.00 mm 0.51 in
Weight	17.98 g 0.04 lb

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Moisture Resistance Test Method	IEC 60068-2-3
Mechanical Shock Test Method	IEC 60068-2-27
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6
Corrosion Test Method	IEC 60068-2-11

Standard Conditions

Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F

SMALL-CAPKIT

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Immersion Depth	Immersion at specified depth for 24 hours
-----------------	---