

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switch.
3-Pole 3-Fuse and solid neutral Fused in a type 1 enclosure (indoor).
Rated 600VAC (30A).



Installation location	INDOOR
Manner of function of the actuating element	SINGLE THROW
Mechanical service life (switching cycles) typical	10000
Mounting type	2 OR 3 POINT MOUNTING HOLES
Number of poles	3
Electricity	
Ampacity	30 A
Supply voltage frequency rated value 50/60 Hz	Yes
Voltage between phase and phase rated value	600 V
Switching capacity	
Switching capacity active power	4 W
Environmental conditions	
Ambient temperature during operation maximum	120 °C
Ambient temperature during operation minimum	-20 °C
Model	
product brandname	SIEMENS
Product type designation	ENCLOSED/SAFETY SWITCH

Mechanical Design	
Design of the housing	TYPE 1
Material	STEEL
General product approval	
Certificate of suitability	UL
last modified:	06/29/2017