

Component Video (RCA) over IP Extender Transmitter over Cat5/Cat6, RS-232 and IR Control, 1080i, 328 ft. (100 m), TAA

MODEL NUMBER: **B160-001-CSI**



Description

The B160-001-CSI Component Video (RCA) over IP Extender Transmitter works with a Tripp Lite B160-Series receiver (sold separately) to extend and distribute component video, stereo audio, RS-232 serial and IR (infrared) remote signals from the source to the display located up to 328 feet (100 meters) away, which is more than 200 feet farther than a traditional Cat5e/6 solution. By adding a chain of low-cost unmanaged network switches, such as Tripp Lite's [NG5](#), you can continue extending the distance between source and display up to 328 feet per switch.

The B160-001-CSI displays a single source on a single display or distributes a single signal to multiple displays. Create a multi-in, multi-out installation with up to 64 transmitters and 255 receivers* by connecting dedicated managed Ethernet network switches** with Internet Group Management Protocol (IGMP), such as Tripp Lite's [NSS-G16D2](#).

With a compatible B160-Series receiver, you can send the component video and stereo audio to any analog or digital display, including DisplayPort™, HDMI and VGA, allowing you to mix and match technologies and use existing monitors. An IGMP-enabled switch will let you manage all connections for centralized control over which sources show on which displays.

The B160-001-CSI supports video resolutions up to 1080i. It mounts to a wall, rack or pole using the included hardware. An HDMI output port allows connection of a local display.

Highlights

- Compatible with Tripp Lite B160-Series A/V over IP receivers
- Video source can be sent to any analog or digital display
- Supports video resolutions up to 1080i
- HDMI output on transmitter for connecting local display
- Plug and play—no software or drivers required

Package Includes

- Transmitter unit
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Plug adapters for North America, U.K., Europe and Australia
- IR-Out cable
- 3.5 mm to DB9 adapter cable (M/F)
- Mounting hardware
- Owner's manual

**Unmanaged switch installations are limited to two transmitter units. Number of receivers is limited to number of ports remaining on unmanaged switch.*

***B160-Series designed for use with dedicated network switch. Connecting to a switch used with other networking equipment will result in degraded or non-functional performance.*



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Features

Distributes Component Video, Stereo Audio, Serial and IR Control Signals over Cat5/6 Cabling

- Converts audio and video to an IP-based signal that is transmitted point-to-point to a display 328 ft. away
- Add low-cost network switches between transmitter and receiver to continue extending distance up to 328 ft. per switch
- HDMI output for connecting a local display

Create a Multi-In, Multi-Out Installation Using B160-Series Transmitters and Receivers

- Connect up to 64 transmitters and 255 receivers through multiple dedicated managed network switches
- IGMP-enabled switches allow centralized control over which sources show on which displays
- Video source can be sent to any analog or digital display, so you can mix and match technologies and use existing monitors

Enhanced Technical Features

- Supports video resolutions up to 1080i
- Uses H.264 video compression standard
- Transmits on 20–60 kHz IR frequency
- Sends IR control signals that control a source from a remote display
- Supports RS-232 serial baud rates up to 57600 Bps
- HDCP and 3D compatible

Plug-and-Play Functionality

- Plug and play—no software or drivers required
- Hardware included for mounting on wall, rack or pole
- Compatible with all Tripp Lite B160-Series A/V over IP receivers

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

INPUT	
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 1A
External Power Supply Output Specs (V / A)	5V, 2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
External Power Supply Plug(s)	NEMA 1-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; PSE; C-Tick; GS; RoHS
Bus Powered	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45 OUTPUT (GREEN / POWER, ORANGE / SIGNAL), CHANNEL SIGNAL (RED), POWER (GREEN)
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.17 x 10.24 x 6.46
Shipping Dimensions (hwd / cm)	5.51 x 26.01 x 16.41
Shipping Weight (lbs.)	1.59
Shipping Weight (kg)	0.72
Unit Dimensions (hwd / in.)	1.17 x 5.04 x 3.94
Unit Dimensions (hwd / cm)	2.97 x 12.8 x 10.0
Unit Weight (lbs.)	1.59
Unit Weight (kg)	0.72
Material of Construction	METAL
Color	Black
Rackmountable	Yes
ENVIRONMENTAL	
Operating Temperature Range	32 TO 104 F (0 TO 40 C)
Storage Temperature Range	5 TO 122 F (-15 TO 50 C)
Relative Humidity	0% TO 85% RH, NON-CONDENSING
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	328
Max 480P Range (ft)	328
Max 1440 x 900 Range (ft)	328
Max 1080i Range (ft)	328
Max 1080P Range (ft)	328
Max 1920 x 1440 Range (ft)	328
Max 480i Range (ft)	328
Max 640 x 480 Range (ft)	328
Max 800 x 600 Range (ft)	328
Max 1600 x 1200 Range (ft)	328
Max 1920 x 1200 Range (ft)	328
Max 720P Range (ft)	328



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Ports	9
Side A - Connector 1	(5) RCA (FEMALE)
Side B - Connector 1	(2) 3.5MM (FEMALE); HDMI (FEMALE); RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1080i
Driver Required	No
Recommended Category Cable	N202-Series Cat6 Patch Cable
EDID Compatible	No
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
3D Video Supported	Yes
CERTIFICATIONS	
Certifications	Tested to CE, FCC, ROHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>