

2



1




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
Q1T2B2C3N24AFA0	X.Xkg (X.Xlb)

- NOTES:
- IDENTIFICATION: VERTICAL, MIXED (18) LOCKING C13 & (6) LOCKING C19, NETWORK-ENABLED MONITORED WITH MONITORED PER OUTLET, 208V / 60A / SINGLE PHASE PDU

PART NO. COLOR
Q1T2B2C3N24AFA0 BLACK

- ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
- PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
- INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY WHEN CONNECTED VIA ETHERNET CONNECTION
- OUTLET LEVEL POWER (AMPS, VOLTS, POWER FACTOR, FREQUENCY) MONITORING CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION
- RoHS COMPLIANT
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- MAXIMUM AVAILABLE INPUT POWER = 10.0 kW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



PLUG
60 AMP, 250V,
2P/3W
IEC 60309, WATERTIGHT

EIGHTEEN (18)
LOCKING RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
LOCKING RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

02A	2-4-15	MRWA	GLM	EDM	RELEASED TO PRODUCTION	12V091QR	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE SMARTZONE NETWORK-ENABLED MPO SERIES RACK PDU Q1T2B2C3N24AFA0 CUSTOMER DRAWING			
ITEM REVISION NAME 12V091QR_02.PRT			
DATASET FILE NAME 12V091QR_DC/02A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR: N/A	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 12V091QR_DC	
DRAWN BY MRWA	DATE 2-4-15	CHK GLM	SCALE NONE
SHT 1 OF 1		SIZE B	