



## PRODUCT DATA SHEET

Zinc-It® Instant Cold Galvanize, 13 Wt Oz  
No. 18412

### Product Description

High-performance coating of >93% pure zinc that electrochemically bonds with ferrous metals to form a galvanic cell. It actively fights rust and corrosion. Use as a touch-up for damaged galvanized coatings. Dries quickly. Outdoor protection: 1 - 2 years.

### Applications

On threads, exposed edges, fasteners, conduit, strapping, welds, fencing, railings, grates, electrical poles, breaker panel housings, rain spouts, signs, doors, trailers, waste containers, catwalks, and guard rails.

### Unit Package Description

16 Ounce Aerosol

### Brand

CRC

### Generic Description 1

Instant Cold Galvanized Coating

### Net Fill

13 Wt Oz

### UPC Code

078254184128

### Unit Dimensions

7.75H x 2.63W x 2.63D in

### Units Per Case

12

### Case Dimensions

8.69H x 8.44W x 11.31D in

### Cases Per Pallet

75

### Case Weight

14 lbs

### I 2 of 5 Code

30078254184129

### Appearance

Gray Viscous Liquid

### Flash point (F)

-2°F

### Flash point (C)

-19&#176;C

### Flammability Class - CPSC

Extremely Flammable

### Spec Gravity Concentrate

0.77 to 0.85

### Plastic Safe

Yes

### Dry Time - Fully Dry

8 Hours

### Dry Time - Tack Free

20 Minutes

### Recoat

Before 1 Hour or After 48 Hours

### Coverage

28 to 32 Sq Ft at 3 Mil Dry



Last revised: 2/13/2017  
Page 1 of 2



Customer Care: 800-556-5074  
Technical Assistance: 800-521-3168  
www.crcindustries.com

CRC Industries is a worldwide leader in the production of specialty chemicals for maintenance and repair professionals serving industrial, electrical, aviation, automotive and marine markets. CRC is ISO 9001:2008 certified and adheres to the strictest guidelines for quality in all facets of research, development and production.



CRC®, K&W®, Sta-Lube®, Marykate® and products denoted with ® and ™ are trademarks of CRC Industries, Inc.



## PRODUCT DATA SHEET

Working Temp (F)	130°F (Continuous) / 150°F (Intermittent)
Working Temp (C)	54.4°C (Continuous) / 65.6°C (Intermittent)
Propellant	Hydrocarbon
Aerosol Flammability Level	III
Military Specification Number	Meets requirements of Mil-P-21035B, Meets requirements of Mil-P-26915, Meets requirements of Mil-P-46105
DOT Proper Shipping Name	Aerosols, Flammable, Limited Quantity
VOC % (Federal)	45.6
VOC g/L (Federal)	555.6
VOC Lbs./Gal. (Federal)	4.64
VOC Category	Aerosol Coating: Metallic
MIR Limit (EPA)	1.9
MIR Limit (CA)	1.25
MIR Value	1.2
Removal (How To)	Remove with aromatic solvents, Xylene. Toluene can be used, but is not recommended.



Last revised: 2/13/2017  
Page 2 of 2



Customer Care: 800-556-5074  
Technical Assistance: 800-521-3168  
www.crcindustries.com

CRC Industries is a worldwide leader in the production of specialty chemicals for maintenance and repair professionals serving industrial, electrical, aviation, automotive and marine markets. CRC is ISO 9001:2008 certified and adheres to the strictest guidelines for quality in all facets of research, development and production.



CRC®, K&W®, Sta-Lube®, Marykate® and products denoted with ® and ™ are trademarks of CRC Industries, Inc.