

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

Date of issue: 16/11/2015

Revision date: 29/12/2015

Version: 2.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
 Trade name : Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Use of the substance/mixture : Temperature indicator

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

LA-CO Industries Europe S.A.S.
 Parc Industriel de la Plaine de
 l'Ain - Allée des Combes.
 01150.BLYES.France.
 Phone: +33 (0)4 74 46 23 23
 Fax: +33 (0)4 74 46 23 29
 E-mail: info@eu.laco.com
 Web: http://www.markal.com

1.4. Emergency telephone number

Emergency number : 24-hour emergency: CHEMTREC- U.S. : 1-800-424-9300 International: +1-703-527-3887

EU Member State	Officieel adviesorgaan	Adres	Noodnummer
AUSTRIA	Vergiftungsinformationszentrale (Poisons Information Centre)	Allgemeines Krankenhaus Waehringer Geurtel 18-20 1090 Wien	+43 1 406 43 43
BELARUS	The Belarus Republican Poisons Centre	Kizhevatova str. 58 Minsk 220115	+375 (0)17 201 9158
BELGIUM	Centre Anti-Poisons/Antigifocentrum c/o Hôpital Central de la Base - Reine Astrid	Rue Bruyn 1 B -1120 Bruxelles/Brussel	+32 70 245 245
BULGARIA	Национален токсикологичен информационен център National Clinical Toxicology Centre, Emergency Medical Institute "Pirogov"	21 Totleben Boulevard 1606 SOFIA	+359 2 9154 409
CROATIA	Poisons Control Centre Institute of Medical Research & Occupational Health	Ksaverska Cesta 2 P.O. Box 291 HR-10000 Zagreb	+385 1 234 8342
CZECH REPUBLIC	Toxikologické informační středisko Clinic For Occupational Medicine, 1st Medical Faculty, Charles University	Na Bojišti 1 120 00 Praha 2	+42 2 2491 9293 +42 2 2491 5402
DENMARK	Giftlinjen Bispebjerg Hospital	Bispebjerg Bakke 23, 60, 1 DK-2400 København NV	+45 82 12 12 12 +45 35 31 55 55
ESTONIA	Mürgistusteabekeskus	Gonsiori 29 15027 Tallinn	+372 626 93 90
FINLAND	Myrkytystietokeskus	P.O.B 340 (Haartmaninkatu 4) HUS SF - 00029 Helsinki	+358 9 471 977
FRANCE	ORFILA		+33 1 45 42 59 59
GERMANY	Berliner Betrieb für Zentrale Gesundheitliche Aufgaben	Oranienburger Strasse 285 13437 Berlin	+49 30 19240
GERMANY	Informations und Beratungszentrum für Vergiftungsfälle	Kirrberger Straße, Gebäude 9 D-66421 Homburg/Saar	+49 6841 19240
GERMANY	Beratungstelle bei Vergiftungen, Klinische Toxikologie und Beratungsstelle bei Vergiftungen	Langenbeckstrasse 1 55131 Mainz	+49 6131 19240
GREECE	Poisons Information Centre	11527 Athens	+30 10 779 3777
HUNGARY	Országos Kémiai Biztonsági Intézet (National Institute of Chemical Safety) Egészségügyi Toxikológiai Tájékoztató Szolgálat (Health Toxicological Information Service)	1437 Budapest PO Box 839 1097 Budapest, Nagyvárad tér 2	+36 80 20 11 99
ICELAND	Eitrunarmiðstöðin	Eitrunarmiðstöðin 108 Reykjavik	+354 543 22 22

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

IRELAND	National Poisons Information Centre	Beaumont Hospital PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2166
LATVIA	Valsts Toksikoloģijas centra Saindēšanās un zāļu informācijas centrs	2 Hipocrate Street LV 1038 Riga	+371 67 04 24 73
LITHUANIA	Apsinuodijimų kontrolės ir informacijos biuras	Siltnamiu 29 2043 Vilnius	+370 5 236 20 52/+370 687 53 378
MALTA	Medicines & Poisons Info Office	Mater Dei Hospital, Msida MSD 2090 Malta	25450000
NETHERLANDS	Nationaal Vergiftigingen Informatie Centrum National Institute for Public Health and the Environment, NB this service is only available to health professionals	Huispostnummer B.00.118, PO Box 85500 3508 GA Utrecht	+31 30 274 88 88
PORTUGAL	Centro de Informação Antivenenos Instituto Nacional de Emergência Médica (INEM)	Rua Almirante Barroso, 36 1000-013 Lisboa	808 250 143 (for use only in Portugal), +351 21 330 3284
ROMANIA	Biroul pentru Regulamentul Sanitar International si Informare Toxicologica	Str. Dr. Leonte Anastasievici Nr.1-3, Sector 5 50463 Bucuresti	+40 21 318 36 06
SLOVAKIA	Národné toxikologické informačné centrum University Hospital Bratislava	Limbová 5 833 05 Bratislava	+421 2 54 77 4 166
SPAIN	Servicio de Información Toxicológica Instituto Nacional de Toxicología, Departamento de Madrid	Calle Luis Cabrera 9 E-28002 Madrid	+34 91 562 04 20
SWEDEN	Giftinformationscentralen Swedish Poisons Information Centre, Karolinska Hospital	Box 60 500 SE-171 76 Stockholm	+46 8 33 12 31 (International) 112 (National)
SWITZERLAND	Centre Suisse d'Information Toxicologique	Freiestrasse 16 Postfach CH-8028 Zurich	+41 44 251 51 51 (International) 145 (National)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Carc. 2 H351

Full text of hazard classes and H-statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS08

Signal word (CLP) : Warning
Hazardous ingredients : Carbon black
Hazard statements (CLP) : H351 - Suspected of causing cancer (if inhaled)
Precautionary statements (CLP) : P201 - Obtain special instructions before use
P202 - Do not handle until all safety precautions have been read and understood
P280 - Wear protective gloves
P308+P313 - IF exposed or concerned: Get medical advice/attention
P405 - Store locked up
P501 - Dispose of contents/container to an authorised waste collection point

2.3. Other hazards

PBT: not yet assessed

vPvB: not yet assessed

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
2',4'-dimethylacetoacetanilide	(CAS No) 97-36-9 (EC no) 202-576-0	0 – 90	Acute Tox. 4 (Oral), H302
Carbon black	(CAS No) 1333-86-4 (EC no) 215-609-9	0.1 – 15	Carc. 2, H351
Polyethylene Glycol	(CAS No) 25322-68-3 (EC no) 500-038-2	0 – 2	Not classified
butyl 4-hydroxybenzoate	(CAS No) 94-26-8 (EC no) 202-318-7	0 – 2	Skin Irrit. 2, H315 Eye Irrit. 2, H319 STOT SE 3, H335

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

- First-aid measures general : Never give anything by mouth to an unconscious person.
- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing. Get medical advice/attention if you feel unwell.
- First-aid measures after skin contact : Gently wash with plenty of soap and water.
- First-aid measures after eye contact : In case of contact, immediately flush eyes with plenty of water.
- First-aid measures after ingestion : Call a POISON CENTER or doctor/physician if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after inhalation : May cause cancer by inhalation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire.
- Unsuitable extinguishing media : None known.

5.2. Special hazards arising from the substance or mixture

- Fire hazard : No particular fire or explosion hazard.

5.3. Advice for firefighters

- Firefighting instructions : Do not allow run-off from fire fighting to enter drains or water courses.
- Protection during firefighting : Wear a self contained breathing apparatus. Wear fire/flame resistant/retardant clothing. EN469.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Avoid creating or spreading dust.

6.1.1. For non-emergency personnel

- Protective equipment : Wear suitable gloves.
- Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

- Protective equipment : Wear suitable gloves.
- Emergency procedures : Stop leak if safe to do so. Ventilate area.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

- For containment : Contain and collect as any solid.
- Methods for cleaning up : Sweep or shovel spills into appropriate container for disposal. Sweep spilled substance into containers; if appropriate, moisten first to prevent dusting.

6.4. Reference to other sections

Section 13: disposal information. Section 7: safe handling. Section 8: personal protective equipment.

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Avoid creating or spreading dust.
- Hygiene measures : Do not eat, drink or smoke when using this product. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

7.2. Conditions for safe storage, including any incompatibilities

- Incompatible products : Strong acids. Strong bases. Strong oxidizers.
- Heat and ignition sources : Keep away from heat, sparks and flame.
- Prohibitions on mixed storage : Incompatible materials.
- Storage area : Store in dry, cool, well-ventilated area.

7.3. Specific end use(s)

Temperature indicator.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Carbon black (1333-86-4)		
Belgium	Limit value (mg/m ³)	3.5 mg/m ³
Denmark	Grænseværdie (langvarig) (mg/m ³)	3.5 mg/m ³
Denmark	Anmærkninger (DK)	K
Finland	HTP-arvo (8h) (mg/m ³)	3.5 mg/m ³
Finland	HTP-arvo (15 min)	7 mg/m ³
France	VME (mg/m ³)	3.5 mg/m ³
Ireland	OEL (8 hours ref) (mg/m ³)	3.5 mg/m ³
Ireland	OEL (15 min ref) (mg/m ³)	7 mg/m ³
Spain	VLA-ED (mg/m ³)	3.5 mg/m ³
Sweden	nivågränsvärde (NVG) (mg/m ³)	3 mg/m ³
United Kingdom	Local name	Carbon black
United Kingdom	WEL TWA (mg/m ³)	3.5 mg/m ³
United Kingdom	WEL STEL (mg/m ³)	7 mg/m ³
Norway	Grenseverdier (AN) (mg/m ³)	3.5 mg/m ³
Polyethylene Glycol (25322-68-3)		
Austria	MAK (mg/m ³)	1000 mg/m ³ (einatembare Fraktion)
Austria	MAK Short time value (mg/m ³)	4000 mg/m ³ max. 4x15 min./Schicht (einatembare Fraktion)
Denmark	Grænseværdie (langvarig) (mg/m ³)	1000 mg/m ³
Denmark	Grænseværdie (kortvarig) (mg/m ³)	2000 mg/m ³
Denmark	Anmærkninger (DK)	(Polyethylenglycol (PEG) med middelmolvægt på 200-600)
Germany	TRGS 900 Occupational exposure limit value (mg/m ³)	1000 mg/m ³
Germany	TRGS 900 Limitation of exposure peaks (mg/m ³)	8000 mg/m ³
Germany	Remark (TRGS 900)	(einatembare Fraktion)
Slovakia	NPHV (priemerná) (mg/m ³)	1000 mg/m ³
Slovakia	Upozornenie (SK)	krátkodobý: kategória II.
Switzerland	VME (ppm)	1000 ppm
Switzerland	Remark (CH)	(mittlere Molmasse 200–600)

8.2. Exposure controls

- Appropriate engineering controls : Ensure good ventilation of the work station.
- Personal protective equipment : Avoid all unnecessary exposure.
- Hand protection : Use rubber gloves. EN374.
- Eye protection : EN166. In case of dust production: protective goggles.
- Respiratory protection : In case of inadequate ventilation wear respiratory protection. Use air-purifying respirator equipped with particulate filtering cartridges. EN 12083.
- Environmental exposure controls : Prevent leakage or spillage.

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

Other information : Do not eat, drink or smoke when using this product.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Solid
Appearance : A solid crayon-like marker.
Colour : Variable.
Odour : No data available
Odour threshold : No data available
pH : No data available
Relative evaporation rate (butyl acetate=1) : No data available
Melting point : No data available
Freezing point : No data available
Boiling point : No data available
Flash point : No data available
Auto-ignition temperature : No data available
Decomposition temperature : No data available
Flammability (solid, gas) : No data available
Vapour pressure : No data available
Relative vapour density at 20 °C : No data available
Relative density : No data available
Solubility : No data available
Log Pow : No data available
Viscosity, kinematic : No data available
Viscosity, dynamic : No data available
Explosive properties : No data available
Oxidising properties : No data available
Explosive limits : No data available

9.2. Other information

VOC content : 0 %

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reactions known.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Heat.

10.5. Incompatible materials

Strong acids. Strong bases. Strong oxidizers.

10.6. Hazardous decomposition products

Carbon oxides (CO, CO₂).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

2',4'-dimethylacetanilide (97-36-9)	
LD50 oral rat	1995 mg/kg
ATE CLP (oral)	1995.000 mg/kg bodyweight
butyl 4-hydroxybenzoate (94-26-8)	
LD50 oral rat	13200 mg/kg
ATE CLP (oral)	13200.000 mg/kg bodyweight

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

Carbon black (1333-86-4)	
LD50 oral rat	> 8000 mg/kg
LC50 inhalation rat (mg/l)	> 4.6 mg/m ³ 4 h
Polyethylene Glycol (25322-68-3)	
LD50 oral rat	47000 mg/kg
LD50 dermal rat	> 20000 mg/kg
ATE CLP (oral)	47000.000 mg/kg bodyweight
Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Suspected of causing cancer (if inhaled).
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: Not classified
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

2',4'-dimethylacetoacetanilide (97-36-9)	
LC50 fish 1	250 (250 - 350) mg/l
Polyethylene Glycol (25322-68-3)	
LC50 fish 1	> 100 mg/l
LC50 other aquatic organisms 1	1000 mg/l

12.2. Persistence and degradability

2',4'-dimethylacetoacetanilide (97-36-9)	
Biodegradation	25 % 28 d
Carbon black (1333-86-4)	
Persistence and degradability	Not readily biodegradable.

12.3. Bioaccumulative potential

2',4'-dimethylacetoacetanilide (97-36-9)	
Log Pow	1.4

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)	
PBT: not yet assessed	
vPvB: not yet assessed	

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Sewage disposal recommendations	: Do not dispose of waste into sewer.
Waste disposal recommendations	: Dispose in a safe manner in accordance with local/national regulations.
European List of Waste (LoW) code	: For disposal within the EC, the appropriate code according to the European Waste Catalogue (EWC) should be used.
H code	: H7 - 'Carcinogenic': substances and preparations which, if they are inhaled or ingested or if they penetrate the skin, may induce cancer or increase its incidence.

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

Not considered a dangerous good for transport regulations

14.2. UN proper shipping name

Proper Shipping Name (ADR) :

14.3. Transport hazard class(es)

Not applicable

14.4. Packing group

Not applicable

14.5. Environmental hazards

Other information : No supplementary information available.

14.6. Special precautions for user

14.6.1. Overland transport

No additional information available

14.6.2. Transport by sea

No additional information available

14.6.3. Inland waterway transport

Carriage prohibited (ADN) : No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

VOC content : 0 %

15.1.2. National regulations

Germany

Water hazard class (WGK) : 1 - low hazard to waters

WGK remark : Classification based on the components in compliance with Verwaltungsvorschrift wassergefährdender Stoffe (VwVwS)

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

according to Regulation (EU) 2015/830

Indication of changes:

Added product

Abbreviations and acronyms:

	ATE: Acute Toxicity Estimate
	CAS (Chemical Abstracts Service) number
	CLP: Classification, Labelling, Packaging.
	EC50: Environmental Concentration associated with a response by 50% of the test population.
	GHS: Globally Harmonized System (of Classification and Labeling of Chemicals).
	LD50: Lethal Dose for 50% of the test population
	OSHA: Occupational Safety & Health Administration
	PBT: Persistent, Bioaccumulative, Toxic
	TWA: Time Weighted Average

Tempilstik® 185 °F (85 °C), 188 °F (87 °C), 250 °F (121 °C), 425 °F (218 °C), 428 °F (220 °C), 1250 °F (677 °C), 248 °F (120 °C)

Safety Data Sheet

according to Regulation (EU) 2015/830

TSCA: Toxic Substances Control Act

Data sources : ESIS (European chemical Substances Information System; accessed at: <http://esis.jrc.ec.europa.eu/index.php?PGM=cla>.
European Chemicals Agency (ECHA) C&L Inventory database. Accessed at <http://echa.europa.eu/web/guest/information-on-chemicals/cl-inventory-database>.
Kristen Forsberg and S.Z. Mansdorf, "Quick Selection Guide to Chemical Protective Clothing", Fifth Edition.
National Fire Protection Association. Fire Protection Guide to Hazardous Materials; 10th edition.
REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of R-, H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Carc. 2	Carcinogenicity, Category 2
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H302	Harmful if swallowed
H315	Causes skin irritation
H319	Causes serious eye irritation
H335	May cause respiratory irritation
H351	Suspected of causing cancer

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Carc. 2	H351	Calculation method
---------	------	--------------------

LA-CO EU CLP SDS

SDS Prepared by: The Redstone Group, LLC
6077 Frantz Rd.
Suite 206
Dublin, OH USA 43016
T 614-923-7472
www.redstonegrp.com

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product