




UN874048604/10 | CS44P GRN C6A 4/23 F/UTP RL 1 KFT CS44P ETL Verified Category 6A F/UTP Cable, plenum, green jacket, 4 pair count, 1000 ft

(305 m) length reel

#### **Product Classification**

Portfolio	Uniprise®
Product Type	Twisted pair cable
Regional Availability	North America

#### **Cross Section Drawing**



#### **Construction Materials**

Jacket Material	PVC
Conductor Material	Bare copper
Drain Wire Material	Tinned copper
Insulation Material	FEP
Separator Material	FEP

#### **Dimensions**

Cable Length	305 m   1000 ft
Cable Weight	39.00 lb/kft
Diameter Over Jacket	7.010 mm   0.276 in



UN874048604/10 | CS44P GRN C6A 4/23 F/UTP RL 1KFT

#### **Electrical Specifications**

ANSI/TIA Category	6A
dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	8.00 ohms/100 m
Delay Skew, maximum	45 ns
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	70 %
Operating Frequency, maximum	500 MHz
Transmission Standards	ANSI/TIA-568-C.2
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac   2500 Vdc

#### **Environmental Specifications**

Environmental Space	Plenum
Smoke Test Method	CMP
Flame Test Method	CMP
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

#### **General Specifications**

Cable Type	F/UTP (shielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Green
Product Number	CS44P
Brand	Uniprise®
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Drain Wire Gauge	24 AWG
Drain Wire Type	Solid
Separator Type	Isolator

#### **Mechanical Specifications**

Pulling Tension, maximum 11 kg | 25 lb

#### **Regulatory Compliance/Certifications**

AgencyClassificationRoHS 2011/65/EUCompliantISO 9001:2008Designed, manufactured and/or distributed under this quality management system



©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: October 10, 2017

UN874048604/10 | CS44P GRN C6A 4/23 F/UTP RL 1KFT





UN874048604/10 | CS44P GRN C6A 4/23 F/UTP RL 1KFT

### **Electrical Performance**

Std Typ	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above Typical
IL	Insertion Loss (dB/100m)
NEXT	Near End Crosstalk (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)
PSNEXT	Power Sum Near End Crosstalk (db/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)
ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)
RL	Return Loss (dB)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	Std	Тур	Std	Тур	Std	Тур	Std	Тур	Std	Тур	Std	Тур	Std	Тур	Std	Тур
1	2.1	1.7	74.3	88.2	72.2	86.5	72.3	85.8	70.2	84.1	67.8	88.9	64.8	86.4	20.0	32.9
4	3.8	3.3	65.3	80.4	61.5	77.1	63.3	78.2	59.5	75.0	55.8	79.7	52.8	77.8	23.0	34.9
8	5.3	4.6	60.8	75.5	55.4	70.8	58.8	73.4	53.4	68.8	49.7	73.7	46.7	71.8	24.5	34.8
10	5.9	5.2	59.3	74.1	53.4	68.9	57.3	72.1	51.4	66.9	47.8	71.9	44.8	69.9	25.0	35.0
16	7.5	6.6	56.2	70.4	48.8	63.8	54.2	68.3	46.8	61.7	43.7	68.2	40.7	66.1	25.0	36.6
20	8.4	7.4	54.8	69.2	46.4	61.8	52.8	67.0	44.4	59.6	41.8	66.2	38.8	64.0	25.0	36.3
25	9.4	8.3	53.3	67.6	44.0	59.3	51.3	65.2	42.0	56.9	39.8	64.2	36.8	62.0	24.3	35.0
31.25	10.5	9.3	51.9	66.1	41.4	56.8	49.9	63.9	39.4	54.6	37.9	62.3	34.9	60.1	23.6	34.5
62.5	15.0	13.2	47.4	60.8	32.4	47.6	45.4	58.7	30.4	45.4	31.9	56.2	28.9	54.1	21.5	31.4
100	19.1	16.9	44.3	57.4	25.2	40.5	42.3	55.4	23.2	38.5	27.8	52.2	24.8	50.2	20.1	27.7
155	24.1	21.2	41.4	54.0	17.4	32.8	39.4	51.9	15.4	30.7	24.0	48.1	21.0	46.0	18.8	24.5
200	27.6	24.3	39.8	50.0	12.2	25.7	37.8	48.5	10.2	24.2	21.8	46.2	18.8	44.1	18.0	22.4
250	31.1	27.3	38.3	50.1	7.3	22.8	36.3	48.2	5.3	20.9	19.8	44.3	16.8	42.2	17.3	21.0
300	34.3	30.0	37.1	48.7	2.9	18.7	35.1	46.7	0.9	16.7	18.3	42.8	15.3	40.3	16.8	19.6
350	37.2	32.6	36.1	46.6	-1.1	14.0	34.1	44.8	-3.1	12.2	16.9	41.6	13.9	39.3	16.3	18.8
400	40.1	35.0	35.3	45.5	-4.8	10.5	33.3	43.8	-6.8	8.7	15.8	39.8	12.8	37.7	15.9	17.9
500	45.3	39.5	33.8	43.8	-11.4	4.2	31.8	41.5	-13.4	2.0	13.8	37.7	10.8	35.5	15.2	16.8
550		41.7		41.8		0.1		40.0		-1.8		35.1		32.7		15.2
650		45.8		34.8		-10.9		33.6		-12.1		33.6		31.2		15.0