

## HDBaseT HDMI over Cat5e/6/6a Extender Transceiver, Serial and IR Passthrough, 4K x 2K @ 30 Hz UHD / 1080p @ 60 Hz, Up to 328 ft. (100 m)

MODEL NUMBER: BHDBT-TR-SI-LR



### Description

Insert the BHDBT-TR-SI-LR HDBaseT HDMI over Cat5e/6/6a Extender Transceiver between the transmitter and receiver units in your Tripp Lite HDBaseT installation to extend the range of your signal. Connect its HDMI port to a projector, monitor or television to expand your installation.

Using a single Cat5e/6/6a cable, the BHDBT-TR-SI-LR transmits uncompressed HDMI audio and video, RS-232 serial and IR control signals up to 328 feet (100 m) from the previous unit in the chain (either the transmitter or another transceiver), including 1920 x 1080 (1080p) signals @ 60 Hz and even Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30 Hz video signals. Add up to five BHDBT-TR-SI-LR Extender Transceivers to the chain for a total range up to 2,000 feet (600 m) with a monitor connected to each transceiver.

RS-232 serial signals and IR remote control signals (@ 39 KHz) also pass through the transceiver, so your HDBaseT installation can control such RS-232 devices as scanners and touchscreen displays at baud rates up to 115 Kbps. You can also operate a Blu-ray player using its remote when at the remote monitor and vice versa. Locking HDMI ports (ideal for use with Tripp Lite's [P569-006-LOCK](#) High-Speed HDMI cables with locking connectors) prevent cables from coming loose or undone, ensuring an intact signal. Attach the BHDBT-TR-SI-LR to a wall, rack or pole using the included hardware.

### Features

#### Extends and Expands Your HDBaseT Installation

- Extends an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30 Hz signal up to 328 feet (100 m)
- Extends a High Definition 1920 x 1080 (1080p) @ 60 Hz signal up to 328 feet (100 m)
- Connects to next link in the chain with just one Cat5e/6/6a cable
- Add up to 5 transceivers to further expand the range of your installation up to 2,000 feet (600 m) with a monitor attached to each transceiver
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio
- Supports 36-bit Deep Color (12 bits per channel), CEC passthrough, 3D video, EDID and HDCP

#### Allows RS-232 and IR Control Passthrough

### Highlights

- Extends and expands your Tripp Lite HDBaseT installation
- Connects multiple monitors at different links in a chain
- Extends both a 4096 x 2160 and 3840 x 2160 (4K x 2K) @ 30 Hz signal up to 328 feet (100 m)
- Extends a 1080p @ 60 Hz signal up to 328 feet (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD

### Package Includes

- BHDBT-TR-SI-LR HDBaseT HDMI over Cat5e/6/6a Extender Transceiver
- External Power Supply with NEMA 1-15P Plug(Input: 100-240V, 50/60 Hz, 0.5A; Output: 5V, 3A)
- Mounting hardware
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- Passes through RS-232 serial signals at 115 Kbps full-duplex baud rates for devices such as scanners and touchscreen monitors
- Passes through IR remote control signals so you can operate your Blu-ray player with its remote while standing at the remote monitor (and vice versa)

#### Easy to Set Up and Use

- Plug-and-play engineering means no software or drivers to download and install
- Inserts quickly between transmitter and receiver in Tripp Lite HDBaseT installation
- Included mounting hardware lets you install each unit on a wall, rack or pole
- Locking HDMI ports (ideal for use with Tripp Lite's [P569-006-LOCK](#) HDMI cables) prevent cables from coming loose or disconnected, ensuring an intact signal

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A
PHYSICAL	
Unit Dimensions (hwd / in.)	1.2 x 5 x 4
Included Mounting Accessories	Y
Color	Black
Unit Weight Details	1lb.
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	328
Max 480P Range (ft)	328
Max 1440 x 900 Range (ft)	328
Max 1080i Range (ft)	328
Max 1080P Range (ft)	328
Max 1920 x 1440 Range (ft)	328
Max 2560 x 1600 Range (ft)	328
Max 4K UHD Range (ft)	328



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Max 480i Range (ft)	328
Max 640 x 480 Range (ft)	328
Max 800 x 600 Range (ft)	328
Max 1600 x 1200 Range (ft)	328
Max 1920 x 1200 Range (ft)	328
Max 2048 x 1536 Range (ft)	328
Max 720P Range (ft)	328
<b>CONNECTIONS</b>	
Ports	0
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
10/100 Ethernet Extension Support	No
<b>CERTIFICATIONS</b>	
Approvals	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>