# 7160 Electric Strike










7160 Electric Strikes with 4-7/8" faceplates are designed for mortise or cylindrical type locksets with up to 3/4" latchbolt projection without deadbolt. For use in aluminum jambs.

# **Function**

Remote electrical control of any door equipped with a mortise or cylindrical type lockset with up to 3/4" latchbolt projection without deadbolt. Electrical actuation unlocks strike jaw, releasing latchbolt so door can be opened without operating latch itself. Extremely compact mechanism fits into aluminum jamb (or opposing door) sections as shallow as 1-7/8". Fits existing prep for discontinued Adams Rite 7560, 7860 Electric Strikes.



# **Specifications**

## FAIL-SAFE/FAIL-SECURE

 Field convertible from one mode to the other.
 However, AC intermittent solenoid must not be used continuously in either.

#### CASE

Approximately 1" x 3-3/8" x 1-7/8" deep.

### **STRIKE LIP**

Basic 7160 strike has lip of proper length for 1-3/4"
thick door that closes flush with jamb edge. Where
door thickness or jamb shape differs from this standard
relationship, lip extension kits are available, specified by
last dash number.

#### **STRIKE OPENING**

 3/4" x 1-7/16" x 5/8" deep. Bolt retainer jaw is stainless steel. Strike location must be centered on latchbolt.

#### **FACEPLATE**

 Measures 1-1/4 x 4-7/8". Faceplate is flat, with radiused corners. Available in a wide range of architectural finishes.

#### **VOLTAGE**

 Available in 12 or 24 volt AC and DC. DC continuous units are silent, AC intermittent units "buzz" on operation.

## **CURRENT DRAW/AMPS**

VOLTS	AC INTERMITTENT	DC CONTINUOUS
12	1.42	0.33
24	0.74	0.17

## STANDARD PACKAGE

 Individually boxed with mounting screws, mounting clips, and adhesive shims to accommodate jamb extrusion thickness greater or less than nominal 1/8".


## **OPTIONS**


 Available with two monitoring signal switches which sense whether latchbolt is in strike and whether strike jaw is blocked. Choice of voltage in AC and DC for intermittent or continuous duty. Specify assembled for either fail-secure (locked when unpowered) or fail-safe (locked when powered) operation, but can be field converted to the other mode.




All measurements are approximate and are provided for informational purposes only. Refer to the product Installation Instructions.

# **Dimensions** Nominal, subject to tolerance extremes







# HOW TO ORDER 7160 ELECTRIC STRIKE Specify quantity and the following information. Order related products separately.

PRODUCT NO.	VOLTAGE	CURRENT AND DUTY	FEATURES*	FINISH	LIP EXTE (Door Center	NSIONS (DIM. A) line to Jamb Edge)
7160	-3	1	0	-628		00
	<b>3</b> 12 Volt	1 DC Continuous or Intermittent	0 Standard/Fail-Secure	313 Dark Bronze Anodized	<b>00</b> 1-1/16" or less	<b>05</b> 2"
	<b>4</b> 16 Volt	4 AC Intermittent	5 Fail-Safe	335 Black Anodized	<b>01</b> 1-1/2"	07 2-1/4"
	<b>5</b> 24 Volt		7 Monitor/Fail-Safe	626 Satin Chrome	<b>02</b> 1-5/8"	09 2-1/2"
			9 Monitor/Fail-Secure	628 Clear Anodized	03 1-3/4"	<b>12</b> 2-7/8"

<sup>\*</sup>Fail-secure can be field converted to fail-safe or vice-versa

RELATED PRODUCTS When purchasing this product, please consider the following related products, available separately:

Options	Power	Deadlatches
Lip extensions.	4603 Rectifier, 4605/4606 Transformer, Piezo Horn audible indicator, PS-1.	4500 and 4900 Series Deadlatches. Note that 4700 Deadlatch is discontinued and replaced by 4900 Deadlatch.