


QuickPort® Field-Configurable Single-Gang & Dual-Gang Multi-Port Wallplates with Designation ID Kit

APPLICATION

Single-gang and dual-gang wallplates accept QuickPort® snap-in modules to support multimedia station applications with 1-, 2-, 3-, 4-, 6-, 8-, and 12-ports. Use where port ID windows in a single-gang or dual-gang economical flush-mount housing is desired.



SPECIFICATION

The wallplate housing shall be a one-piece, single- or dual-gang flush mount style that fits standard NEMA openings. It should provide 1-, 2-, 3-, 4-, 6-, 8-, or 12-ports. Must be able to accept all Leviton QuickPort modules. It must be made of high-impact, fire-retardant plastic rated UL 94V-0, and be UL Listed, CSA Certified, and compliant with FCC Part 68 and TIA/EIA-568-B specifications. Colors, port counts and configurations to be specified per schedule on plan. Wallplate screws must match wallplate color.

FEATURES

- Color choice of white or ivory.
- Station ID designation windows for each wallplate.
- Color-matched wallplate screws.
- Fits within minimum rectangular NEMA openings.
- Compatible with all individual QuickPort modules.
- Individual-port configurability allows specification flexibility.
- Narrow module width allows high port density in a small area.
- Manufactured in Mexico.

DESIGN CONSIDERATIONS

- Single-gang fits standard NEMA single-gang backboxes; Dual-gang fits both single- and dual-gang standard NEMA back boxes.
- Install blanks (PN# 41084-B*B) in unused ports for future expansion.
- Specify port identification method (colored modules, designation labels and custom silkscreening available). To ID ports, use different colored jacks for each application (full selection of TIA/EIA-606 compatible colors, 14 available), or Leviton's pre-printed Port Designation Labels. (PN#: 41080-LXB).
- Higher port versions (4-, 6-, 8-, and 12-ports) may be used for MUTO (multi-user telecommunications outlet) applications.

STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: UL Listed; CSA Certified; complies with TIA/EIA-568-B; and meets FCC Part 68.

PHYSICAL SPECIFICATIONS

- Dimensions: Single-gang: 4.53"H x 2.75"W x .925"D (in-wall depth, loaded)
Dual-gang: 4.53"H x 4.625"W x .925"D (in-wall depth, loaded)
- Capacity: Single-gang: Available in 1-, 2-, 3-, 4-, or 6-port
Dual-gang: Available in 1-, 2-, 3-, 4-, 6-, 8-, or 12-port
- Materials: High-impact, fire-retardant plastic rated UL 94V-0


WARRANTY INFORMATION

For a copy of Leviton product warranties, log on to www.leviton.com/warranty.

46080-xxS, 46060-xxP

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



46080-xxS, 46060-xxP

QuickPort® Single-Gang Wallplates with Designation ID Windows

Description	Part No.
6-Port Wallplate, 2 ID Windows	46080-6*S
4-Port Wallplate, 2 ID Windows	46080-4*S
3-Port Wallplate, 2 ID Windows	46080-3*S
2-Port Wallplate, 2 ID Windows	46080-2*S
1-Port Wallplate, 1 ID Window	46080-1*S

QuickPort Dual-Gang Wallplates with Designation ID Windows

Description	Part No.
12-Port Wallplate, 4 ID Windows	46080-12*
8-Port Wallplate, 4 ID Windows	46080-8*P
6-Port Wallplate, 4 ID Windows	46080-6*P
4-Port Wallplate, 4 ID Windows	46080-4*P
3-Port Wallplate, 2 ID Windows	46080-3*P
2-Port Wallplate, 2 ID Windows	46080-2*P
1-Port Wallplate, 2 ID Windows	46080-1*P

Note: Housings are sold empty. Snap-in connectors must be ordered separately.

* = Color Choices: White (W), Ivory (I)

