

HDMI over Cat5/Cat6 Extender Kit, Power over Cable, 1080p @ 60 Hz, TAA

MODEL NUMBER: B126-1P1M-U-POC



Description

The B126-1P1M-U-POC HDMI over Cat5/Cat6 Extender Kit includes a transmitter and a low-profile receiver that work in tandem to extend an HDMI audio/video signal to a projector, monitor or television. The kit is recommended for digital signs, trade shows, classrooms, churches, offices, retail settings and other applications where the source is located farther than conventional cables allow.

HDMI cable (see Tripp Lite's P568-Series) connects the audio/video source, such as a Blu-ray™ player, and optional local display to the transmitter's HDMI ports. Cat5e/6/6a cable connects the transmitter to the receiver's RJ45 port (for best results, use 24 AWG solid-wire Cat6 cable, such as Tripp Lite's N202-Series). The receiver plugs directly into the display's HDMI input port. Built-in PoC technology powers the receiver over Cat5e/6/6a cable, so no external power supply on the display side is needed.

The B126-1P1M-U-POC can extend a high-definition 1080p (at 60 Hz) signal up to 50 feet and a 1080i signal up to 100 feet. In addition to crystal-clear video, the B126-1P1M-U-POC delivers full, rich audio up to 7.1-channel surround sound (multi-channel or PCM) and supports 3D and HDCP standards. Easy to set up with no software or drivers to install. Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

Extends a High-Definition HDMI Audio/Video Signal

- Transmitter extends HDMI A/V signal to low-profile receiver
- Recommended for digital signs, trade shows, classrooms, churches, offices, retail settings and other HDMI A/V applications
- Extends a 1080p (@ 60 Hz) signal up to 50 ft. from source
- Extends a 1080i signal up to 100 ft. from source
- Supports 7.1-channel surround sound (multi-channel or PCM) audio
- HDCP and 3D compliant

Easy to Set Up and Use

- Built-in Power over Cable (PoC) technology powers the receiver

Highlights

- Built-in Power over Cable (PoC) technology powers the receiver
- Supports high-definition video resolutions up to 1080p (@ 60 Hz)
- Supports 7.1-channel surround sound audio
- HDCP and 3D compliant
- Plug-and-play operation with no software or drivers required

System Requirements

- Source with HDMI and USB ports (if source has no USB port, a USB wall charger can be used)
- Display with HDMI port

Package Includes

- Transmitter unit
- Receiver unit
- USB Micro-B cable, 1 ft.
- USB Micro-B cable, 3 ft.
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Transmitter and receiver connect with Cat5e/6/6a cable (for best results, use Tripp Lite's N202-Series)
- Transmitter connects to source and optional local display using HDMI cable, such as Tripp Lite's P568-Series
- LEDs indicate when units are receiving power or an HDMI signal
- Plug-and-play operation with no software or drivers required

TAA-Compliant

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

CONNECTIONS	
Ports	2
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
CERTIFICATIONS	
Certifications	Tested to
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>