

## Mobile Flat-Panel Floor Stand for 32" to 70" TVs and Monitors

MODEL NUMBER: **DMCS3270XP**



### Description

The DMCS3270XP Mobile Flat-Panel Floor Stand allows you to mount a flat-panel television, monitor or other display and move it from room to room for best viewing or against a wall out of the way when not in use.

Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms, the height-adjustable mobile stand fits most flat-panel displays from 32 to 70 inches.

You can adjust the DMCS3270XP's height from 47 to 81.5 inches. You can also rotate the display for viewing in portrait or landscape modes. Roll the unit with little effort to the proper viewing location and angle on sturdy four-inch swivel casters that move smoothly through doorways and over thresholds. All four casters lock to keep the stand securely in position.

A shelf mounted above the display holds projectors, webcams and laptops. A lower shelf holds other audio/video components, such as a Blu-ray player. Durable aluminum and steel construction supports up to 110 lb. The adapter brackets can be adjusted to conform to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200, 300 x 300, 400 x 200, 400 x 400 and 600 x 400.

### Features

#### Height-Adjustable Display Stand Rolls from Room to Room

- Mobile mount for flat-panel TVs, monitors and other displays
- Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms
- Fits most flat-panel displays from 32 to 70 in.

#### Flexible Features That Meet Your Specifications

- Height adjusts from 47 to 81.5 in.
- Rotates for viewing in portrait or landscape modes

### Highlights

- Fits most flat-panel displays from 32 to 70 in.
- Designed for portrait or landscape mounting
- Height adjusts from 47 to 81.5 in.
- Locking 4 in. swivel casters for easy movement
- Supports up to 110 lb.

### Package Includes

- Middle base
- Left leg
- Right leg
- Left cover
- Right cover
- Support plate
- Universal plate
- (2) Plastic covers
- (2) Adapter brackets
- Column
- Plastic handle
- Top cover
- Connecting plate
- Camera shelf
- DVD shelf
- (8) Washers
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (8) M6 x 16 screws
- (3) M6 x 25 screws
- (7) M4 x 6 screws
- (2) M6 x 14 screws
- (6) M6 x 8 screws
- (4) M8 x 25 screws
- (2) M5 x 8 screws
- (8) Small spacers
- (8) Big spacers
- Allen wrench
- Wrench



#### Rolls on Sturdy Metal Casters

- 4 in. swivel casters move smoothly through doorways and over thresholds
- All casters lock to hold stand securely in position while at rest

#### Durable Construction

- Made from aluminum and steel
- Upper shelf holds projectors, webcams and laptops
- Lower shelf holds A/V components, such as Blu-ray player
- Supports up to 110 lb.

#### VESA Compliance

- Supports the following VESA mounting hole patterns: 200 x 200, 300 x 300, 400 x 200, 400 x 400 and 600 x 400

- Owner's manual

## Specifications

PHYSICAL	
Unit Dimensions (hwd / in.)	81.5 x 32.6 x 27.6
Unit Weight (lbs.)	46.2
Unit Weight (kg)	20.96
Material of Construction	aluminum/steel
Color	Black; Silver
Screen Size Compatibility (in.)	32 to 70
Screen Size Compatibility (cm)	81.28 x 177.80
VESA Pattern (mm)	200x100; 300x300; 400x200; 400x400; 600x400
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>