

The 8000 available in a **Complete One Box** 

# Solution

# The concealed electric strike solution for **cylindrical** locksets

Series

Shown with 801 Option

### The 8000 series is a compact, high performance electric strike featuring a unique concealed design for use with cylindrical locksets. No cutting on the frame is required. Simply remove the existing strike plate, adjust the vertical alignment feature to the latchbolt centerline, and install. Its strength is derived from a unique keeper pin locking design, enabling the 8000 to exceed the ratings of the frame, door and locking hardware. This field selectable fail secure/fail safe unit is easy to install and accommodates latchbolts up to 5/8" throw.

#### **Specifications**

- UL 1034, burglaryresistant listed and suitable for outdoor use
- UL 294 (6th Edition) listed
- ANSI/BHMA A156.31, Grade 1
- RoHS compliant
- Patents: 5,934,720; 8,146,966; 8,157,302; 8,465,067

#### **Frame Application**

- Metal
- Wood

#### **Electrical**

- .24 Amps at 12 VDC/VAC
- .12 Amps at 24 VDC/VAC
- DC continuous duty/ AC intermittent duty only
- PoE friendly

# 8000 Models

8000

Universal electric strike

Faceplate options ordered separately, see page 38

8000C

Complete electric strike

Includes the 801 and 801A faceplates

RF8010


Integrated Prox

Includes the strike body, Prox reader and door position switch

IC8020

Integrated

Includes the strike body, iCLASS reader and door position switch








Diagram shown with 801 Option

#### **Standard Features**

- No cutting on frame required
- Vertical adjustability to accommodate door sag and misalignment
- Tamper-resistant
- Static strength 1,500 lbs.
- Dynamic strength 70 ft-lbs.
- Endurance 500,000 cycles
- Field selectable fail secure/fail safe
- Dual-voltage 12 or 24 VDC/VAC
- Non-handed
- Internally mounted solenoid
- Accommodates 1/2" 5/8" cylindrical latchbolt (5/8" with 1/8" door gap)

- Strike body depth 1-1/16"
- Strike body width 1-7/16"
- Five-year limited warranty

#### **Optional Features**

LBM » Latchbolt monitor

#### **Accessories**

**2001M** » Plug-in bridge rectifier

2004M » ElectroLynx® adapter

2005M3 » SMART Pac® III

2006M » Plug-in buzzer

#### **Finishes**

630 » Satin stainless

605 » Bright brass

606 » Satin brass

612 » Satin bronze

613 » Bronze toned

629 » Bright stainless steel

**BLK** » Black

\*Complete Pacs are only available in the 630 finish



GRADE 1













## 8000/8300 Series Faceplate Options



**Operation**: After releasing the latchbolt, the keeper returns to the locked position



#### 801 Option

For use with: Cylindrical locksets in ANSI metal jambs, with latchbolts up to 5/8" throw





4-7/8" × 1-1/4"



#### 801A Option

For use with: Cylindrical locksets with latchbolts up to 5/8" throw. Includes universal mounting tabs. Aluminum frames.





Radius corners and flat faceplate

4-7/8" × 1-1/4"



801E Option

For use with: Extended lip for 'knock-down' style frame installations. For use with cylindrical latchbolts up to 5/8" throw.



4-7/8" × 1-1/4" Extended lip



802 Option

For use with: Cylindrical locksets with latchbolts up to 5/8" throw. Includes universal mounting tabs. Aluminum frames.





7-15/16" × 1-7/16"



803 Option

For use with: Cylindrical locksets with latchbolts up to 5/8" throw. Includes universal mounting tabs. Aluminum frames.

)) ANSI/BHMA Numbers: E05031, E09321, E09322, E09323

)) ANSI/BHMA Numbers: E05031, E09321, E09322, E09323



Radius corners and flat faceplate

6-7/8" × 1-1/4"



9" × 1-3/8" Radius corners and flat faceplate

805 Option

For use with: Cylindrical locksets. For use with latchbolts up to 5/8" throw. Four point mounting for wood installations.

)) ANSI/BHMA Numbers: #E05031, #E09321, #E09322, #E09323



"For use with" information is offered as a recommendation only. Reference should be made to the lockset manufacturer for proper installation instructions necessary to meet compatibility requirements.