

100DR | 200DW

N Series: Deadbolt Door & Drawer Cabinet Locks

**ANSI/BHMA Grade 1
E07121 | E07041**

**Woodwork Institute (WI)
acknowledged product**

SPECIFICATIONS

Keying: Can be keyed together with other N Series locks
Rekeyable: Easily rekeyable via set screw cylinder release mechanism

ANSI/BHMA: Passed ANSI/BHMA A156.11
Grade 1 performance requirements. Equivalent to E07121(100DR) / E07041(200DW).

Non-magnetic: See our 100M/200M Series MRI locks

Standard function: Key removable in locked or unlocked position. Standard function locks are non-handed.

Key-retaining: Key removable in locked position only.
Specify handing (KL/KR for doors or KI/KV for drawers) when ordering.

US Patent Nos: 4,899,563; 4,920,774

Body: Zinc die cast

Cylinder: Solid brass, pin tumbler

Cylinder length: 15/16", 1-3/8" or 1-5/8"

Barrel diameter: 7/8"

Finish: 26D, US4 or 10B

Packaged: Packed 10 per box

KEYING INFORMATION

Keyway: N Series (equivalent to National D4291 4-pin or D4292 5-pin system)

Keys: Includes 2 keys per lock

Stock keying: KD/KA - 4 pin standard

Stock KA#: 101, 103, 107, 915

NEW Stock KA#: 51001, 51002, 51003, 51004
(Coming September 2016)

Masterkeyed: 5 pin standard

Grand masterkeyed: Available

Keyblank 4-pin: KBN-4-NP
(equivalent to NA14, 1069L)

Keyblank 5-pin: KBN-5-NP
(equivalent to NA12, 1069LA)

Keyblank 5-pin copper plated: KBN-5B
(use with 100M/200M MRI locks)

INCLUDED ACCESSORIES

100DR: 2 keys, 56-1 bar strike, and lock mounting screws

200DW: 2 keys, 12-3 angle strike, and lock mounting screws

OPTIONAL ACCESSORIES

Spacers: WP21 (3/32" thick), WP22 (1/4" thick), WP23 (1/2" thick)

Strikes: 07S, 12-1, 12-2, 12-3, 12-4, 56-1

Trim collars: TR1256

Through-bolt hardware: ETS2 trim plate, ETS2-PL trim pull and ETST2 template

Extended (long) bolt: 15-1-35 (for use with 100DR or 200DW)



US26D finish



US4 finish



US10B finish

100DR

Function: Cabinet door lock

ANSI/BHMA No. E07121

Barrel length: 15/16" or 1-3/8"

Extended bolt: Extends overall bolt length by 1-1/2".
Specify -LB option at time of order.



56-1



With long-bolt option



US26D finish



US4 finish



US10B finish

200DW

Function: Drawer lock

ANSI/BHMA No. E07041

Barrel length: 7/8", 1-3/8" or 1-5/8"

Extended bolt: Specify -LB option at time of order.



12-3



With long-bolt option

OLYMPUS
LOCK, INC.
The cabinet lock innovators.

100DR | 200DW

ANSI/BHMA Grade 1
E07121 | E07041

N Series: Deadbolt Door & Drawer Cabinet Locks

OPTIONAL ACCESSORIES - See our website for a complete list of optional components.

Internal plastic spacers

- WP21 3/32" thick plastic spacers
- WP22 1/4" thick plastic spacers
- WP23 1/2" thick plastic spacers

Strikes

- 12-1, 12-2, 12-3, 12-4, 07S

Trim Ring

- TR1256 trim ring

Extended bolt

- 15-1-35 (see below for installed dimensions)



Through-bolt plate


External metal 1/8" or 1/4" through-bolt plate allows for an attractive flush mounting of the cabinet lock face. Available in US3 or US26D finish.

- ETS2-125 through-bolt plate, 1/8" thick
- ETS2-250 through-bolt plate, 1/4" thick

Through-bolt plate template

Allows for proper mounting hole placement of through-bolt plate. Can be used as a 1/8" shim spacer. Available in US3 and US26D finish.


- ETST2 through-bolt plate template



U.S. Patent No. D490,686


DIMENSIONS

100DR Cabinet Door Lock



Extended (long)
bolt option for
100DR

200DW Drawer Lock



Extended (long)
bolt option for
200DW