

FREP/CPE

Product Description

EPR Insulation
CPE Jacket
90°C, 600 V



Applications

Designed for power and control, telemetering, relay control, traffic control, switching, lighting and signal transmission. May be used in Class I, Div. 2 and Class II Div 2 Hazardous Locations per NEC Art. 501 and 502. These cables also conform to Art. 392 "Cable Trays" and Art. 336 "Power and Control Tray Cable".

Specification

- CONDUCTORS: Class B stranded tinned copper per ASTM B-3, B-8 and B-33
- INSULATION: Ethylene Propylene Rubber (EPR) per ICEA S-73-532 (NEMA WC57), meets UL 44 requirements for VW-1, Type XHHW-2 conductors
- COLOR CODE: Conductors color coded per ICEA Method 1, Table E-2 (formerly K-2)
- ASSEMBLY: Conductors are cabled with fillers where necessary to make round, two conductor cables are flat
- OVERALL JACKET: Sunlight-resistant Chlorinated Polyethylene (CPE) per UL 1277
- STANDARDS: Meets UL 1277 requirements for Type TC cables having VW-1, XHHW-2 conductors, cables are listed for direct burial and meet the IEEE 1202, IEEE 383 and UL 1685. 70,000 Btu/hr flame tests as well as the ICEA T-29-520, 210,000 Btu/hr flame test
- AMPACITY: Based on not more than three conductors in raceway or cable or earth with an ambient temperature of 30°C and a conductor temperature of 90°C per NEC 310.16, the values have been derated where applicable
- TEMPERATURE: 90°C
- VOLTAGE: 600 V

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Diameters and weights may vary among manufacturers. Other conductor counts available upon request. Unless otherwise specifically permitted in the NEC, the overcurrent protection shall not exceed 15 A for 14 AWG, 20 A for 12 AWG and 30 A for 10 AWG. All part numbers require color code designation. See Color Code Chart in the Technical Information section. For Method 1, Table E-1 color code add-1 to Part No. (e.g. 2MR-1407-1).

Anixter No.	Conductor Size AWG	No. of Conductors	Insulation Thickness (in.)	Overall Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor
2MR-1402	14	2	0.030	0.045	0.230 x 0.365	60	25
2MR-1403	14	3	0.030	0.045	0.390	92	25
2MR-1404	14	4	0.030	0.045	0.425	115	20
2MR-1405	14	5	0.030	0.045	0.465	139	20
2MR-1407	14	7	0.030	0.060	0.505	183	17
2MR-1409	14	9	0.030	0.080	0.620	250	17
2MR-1412	14	12	0.030	0.080	0.700	317	12
2MR-1415	14	15	0.030	0.080	0.755	383	12
2MR-1419	14	19	0.030	0.080	0.815	468	12
2MR-1425	14	25	0.030	0.080	0.935	645	11
2MR-1430	14	30	0.030	0.080	1.030	747	10
2MR-1437	14	37	0.030	0.080	1.110	897	10
2MR-1202	12	2	0.030	0.045	0.245 x 0.400	83	30
2MR-1203	12	3	0.030	0.045	0.435	124	30
2MR-1204	12	4	0.030	0.045	0.475	157	24
2MR-1205	12	5	0.030	0.045	0.520	191	24
2MR-1207	12	7	0.030	0.060	0.595	268	24
2MR-1209	12	9	0.030	0.060	0.695	347	24
2MR-1212	12	12	0.030	0.060	0.765	437	15
2MR-1215	12	15	0.030	0.060	0.880	561	15
2MR-1219	12	19	0.030	0.080	0.940	688	15
2MR-1225	12	25	0.030	0.080	1.095	894	11
2MR-1230	12	30	0.030	0.080	1.150	1,040	11
2MR-1237	12	37	0.030	0.080	1.240	1,256	12
2MR-1002	10	2	0.030	0.045	0.270 x 0.445	112	40
2MR-1003	10	3	0.030	0.045	0.485	172	40
2MR-1004	10	4	0.030	0.060	0.560	234	32
2MR-1005	10	5	0.030	0.060	0.615	284	32
2MR-1007	10	7	0.030	0.060	0.670	381	28
2MR-1009	10	9	0.030	0.080	0.760	488	28
2MR-1012	10	12	0.030	0.080	0.905	651	20

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.