



All measurements are approximate and are provided for informational purposes only. Refer to the product Installation Instructions.


Dimensions




Door Preparation



Installation



Door Preparation  
WITH 8650 ESCUTCHEON\*



\*Other cylinder escutcheons for use with 17mm profile cylinders (in 44 or 55mm thick doors only) are also available and require different door prep than shown.

HOW TO ORDER 4781 TWO-POINT DEADLATCH Specify quantity and the following information. Order related products separately.


Product no.		OPERATION	PADDLE FINISH
4781	T	-021	-628
	T Top rod only	021 Push to LEFT	313 Dark Bronze Anodized US3 Bright Brass
	- Standard rod	041 Push to RIGHT	335 Black Anodized US26 Bright Chrome
		628 Clear Anodized	US26D Satin Chrome

RELATED PRODUCTS When purchasing this product, please consider the following related products, available separately:

<b>Accessories</b> 8650 Cylinder Escutcheon. 8655 Tall Door Kit.	<b>Cylinders</b> 4781 Two-Point Deadlatch is operable by any standard 1-5/32" diameter mortise cylinder with MS® cam. 4036 Mortise Cylinder.	<b>Special Order Options</b> 3080 Entry Trim.
--	--	--

Bolts and Strikes

- The patented top latching mechanism utilizes a rotating top bolt which deadlatches around the header strike, interlocking the door to the frame. Supplied with standard header strike. The hexagonal, hardened steel bottom bolt is shielded in a cast housing for strength and stability.



Options and Accessories

SILENT ELECTRIFICATION MOTORIZED LATCH RETRACTION

- The SE Motorized Latch Retraction option provides near-silent operation for quiet environments such as hospitals, offices, hotels, and libraries where solenoid-driven devices would be disruptive.

ELECTRIC LATCH RETRACTION

- The LR option uses a solenoid mounted in the pushbar for instantaneous unlocking and locking of the exit device from a remote location or access control device. LR option is not available on rim type exit devices (see EL option).

ALARMED EXIT DEVICE

- This battery-operated option emits a loud (95 decibel) alarm to notify management of unauthorized exit. Available on minimum opening width 36". Cannot be ordered with other exit device options.

REQUEST TO EXIT (REX) – MONITOR / SIGNAL SWITCH

- Mounted in the exit device pushbar on the hinge end, the switch can be used to activate signal light, horn, monitor, or other devices.

CYLINDER DOGGING

- For management control of dogging exit devices for life-safety exit devices only.

ELECTRIC DOGGING

- A holding magnet keeps the pushbar depressed (set manually) and the latch retracted for lower profile exit devices, resulting in less damage and quieter operation.

MATCHING END CAPS

- Matching end caps are available for applications where it is preferable that the end caps match the finish of the exit device. Available for US finishes only.

AVAILABLE FINISHES

- 313 Dark Bronze Anodized
- 335 Black Anodized
- 628 Clear Anodized
- US3 Bright Brass
- US4 Satin Brass
- US32 Bright Stainless
- US32D Satin Stainless

For more detailed information on any of the options and accessories listed above please see the Accessories page of the EXIT DEVICE section of this catalog.

HOW TO ORDER 8600 SERIES (LIFE-SAFETY) NARROW STILE CONCEALED VERTICAL ROD EXIT DEVICE

Specify quantity and the following information. Order related products separately.

MODEL	PUSHBAR FINISH	ROD TYPE	DEVICE OPTIONS	MONITORING OPTION	DOOR OPENING WIDTH On pair of doors, specify HALF of the total exit opening	US FINISH	END CAPS OPTION
86	22	T	SE	M2	-36		
86 Life-Safety	00 US Finish	T Top Rod only	LR Electric Latch Retraction	M Single Switch	30 30 inches	US3 Bright Brass	MEC Matching End Caps
	11 Clear Anodized 628	- Standard rod	SE Silent Electrification Latch Retraction	M2 Dual Switch	36 36 inches	US4 Satin Brass	
	22 Dark Bronze Anodized 313		C Cylinder Dogging	(Blank) No Monitor	40 40 inches	US32 Bright Stainless	
	33 Black Anodized 335		ED Electric Dogging		48 48 inches	US32D Satin Stainless	
			(Blank) No Option		AXXB Alarmed Exit Device where XX is door opening width		

NOTE that Alarmed Exit Device option cannot be combined with Device Options or Monitoring Options.  
ALSO NOTE: Split finishes (faceplate/pushbar) are not available.

RELATED ANSI TRIM FUNCTIONS

01 Exit only – no outside operation  Cylinder Type N/A	02 No outside operation – pull only when dogged  N/A	03 Night latch – key retracts latch. Requires 8650 Cylinder Escutcheon kit  Mortise	08 Key outside unlocks/locks lever  Mortise	09 Night latch - key unlocks trim, trim retracts latch/trim relocks when key is removed  Mortise	14 Passage only  N/A
--	---	--	--	---	-------------------------------

Please see TRIM Section of this catalog for information on Pulls and Entry Trim.

RELATED PRODUCTS When purchasing this product, please consider the following related products, available separately:

Accessories REX-Monitor/Signal Kits. 8655 Tall Door Kit. Trim Function 03 (key retracts latch) requires 8650 Cylinder Escutcheon kit.	Cylinders Adams Rite exit devices are operable by either rim or mortise cylinders depending upon the ANSI/BHMA functions of the exit device.	Trim Entry trim and fixed pulls.	Power PS-SE, PS-LR, and 4612 Power Transfer Device.
--	---	-------------------------------------	--