Prox ID card support: With Trilogy durability



Trilogy prox lock with audit trail

PDL3000

PIN/Prox Cylindrical

- Use the same ID cards as hardwired access systems & install in an hour
- Save all the downtime and 1/2 the cost of hardwired systems
- Provide access for up to 2000 users, with prox ID-cards or 3 to 6 digit codes including:
- Master, manager, supervisor and basic user. Users are individually programmed to use a card only, code only, or, for the highest security, both card and code.
- Built-in HID Prox reader for entry with HID125KZ prox ID cards and keyfob credentials
- Grade 1 BHMA Certified durability and rugged clutch mechanism ensure long dependable life
- Weatherproof performance for indoor and outdoor applications, wide operating temperature range of -31°F to +151°F (-35°C to +66°C)
- Electronic master key system with access customized to each user's hours Give each user access to common areas and/or their individual area(s) and do so defined by the actual times they are permitted entry there.
- Tap and Add batch ID card enrollment mode at lock or download from a PC
- 40,000 event audit trail; 500 scheduled events
- PC programming/reporting

- Quick passage mode
- 5AA battery operation; 60,000 cycles, typical

For iClass Prox Locks with 13.56 MHz support for one-card solutions - also see PDL8200 pg 8


PDL8200 – Model also logs mechanical key override use

Trilogy prox only defeats vandals

PL3000

Prox Only Cylindrical

- Keypad-less version of above for ultimate vandal-proofness in harshest environments
- Accepts HID prox cards and keyfobs for access
- Easy Tap & Add batch ID card enrollment mode allows many cards to be quickly added without PC –also- downloadable from PC or enroller tool
- 40,000 event audit trail log, 500 scheduled events
- PC programming/reporting



Trilogy Ordering Information

Choice of three standard Trilogy finishes





IIS10R Duronodio

U.S. Handing options







00 Straight Leve

75 Regal Curved Lever

25 Turnpiece 50 Knob available on DL1250/1350

DL-WINDOWS Trilogy Software

Free Alarm Lock Trilogy Microsoft Windows-based software application, for programming, entering users, receiving audit trail from lock or used with ALDTMs to transfer data. Version.4.177 or higher, supports Trilogy Networx, Wireless Keypads, Locks and ArchiTech series, and Trilogy standalone

locks, with single database. Downloadable free at www.alarmlock.com. For enterprise network software options, and real-time performance, see pg.15

Trilogy audit trail and programming

AL-IR1 Infrared Printer

Prints the event log and user code with hand-held convenience.

AL-DTMIII Data Transfer Module

Module used to transfer program data from the PC to the lock and receive Audit Trail from the lock. Can transfer program data for up to 200 locks.

AL-PRE2 Dual Function Reader/Enroller for Smart Cards or **Prox IDs**

Just tap the Smart Card or Prox ID device to the unit's faceplate to automatically enroll in DL-WINDOWS software database. (9V battery operation.)

AL-PCI2U Lock / PC Interface (shown)


Interface cable interconnects lock and PC for data transfer with USB interface cable. (AL-PCI also includes DL-WINDOWS CD). Also available AL-PCI2 w/o USB.


Remote Release Kit

RR-TRILOGYKIT

Remote release kit for all Trilogy Cylindrical models includes the **RR-1BUTTON** for desk mount applications and **RR-RECEIVER** for installation inside the battery compartment of any cylindrical Trilogy lock (Simply connects to the 2 white remote release wires inside. Retrofits any existing cylindrical Trilogy manufactured since 1994.

Also available for Mortise and Exit Trim models, **RR-MORTISEKIT** and **RR-EXITTRIMKIT**, respectively. (Note: individual kit components, in blue, are also separately available.)






Trilogy Narrow Stile

DL1200/26D1

Model Type PDL – Prox/PIN DL – Digital PIN Trilogy Series 12 – 2700 Series 13 – 3000 Series Trim 00 = Lever 25 = Turnpiece 50 = Knob 75 = Regal lever Finish //26D Satin Chrome /10B Duronodic /MS Metallic Silver /MB Metallic Bronze	Mechanical Dead Latch 1 – Supports Adams Rite: 4710, 4730, 4900 Series 2 – Supports Adams Rite: 4070, MS1850S, MS1850S-050, MS1950, MS1850S-050 3 – KIT Includes Adams Rite 4900 with 1-1/2" backset, 628 & 313 faceplate 4 – KIT Includes Adams Rite 4900 with 1-1/2" backset, 628 & 313 faceplate
--	---





11

Access Control Locks & Special Models

PDL6500	PDL8200	DL1200	P/DL1300	ETDL	ETPDL	P/ETDLN	DL1200ET	P/DL1300ET	DK3000	PDK3000	NETDKPAK	NETPDKPAK	N90S/ST	N955/T	N951/J
Mortise Prox Ethernet	Cylindrical Prox Ethernet	Narrow Stile	Narrow Stile	For use w/ panic device	For use w/ panic device ,Prox	For use w/ panic device Ethernet	Narrow Stile For use w/ panic device	Narrow Stile For use w/ panic device	Standalone Keypad	Standalone Keypad, Prox	Keypad Ethernet	Keypad, Prox Ethernet	Cylindrical Surface Mount, Ethernet	Mortise Surface Mount, Ethernet	Mortise Insert Electronics, Ethernet
000	5000	100	2000	2000	2000	2000	100	2000	2000	2000	5000	5000	5000	5000	5000
6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-5 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits			
eypad /PC	Keypad /PC	Keypad	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Card Reader/PC	Card Reader/PC	Card Reader/PC
ll metal, 2 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button			
traight or urved lever	Straight or curved lever	Straight or curved lever, thumbturn or knob	Straight or curved lever, thumbturn or knob	Straight or curved lever	Straight or curved lever	Straight or curved lever	Straight or curved lever, thumbturn or knob	Straight or curved lever, thumbturn or knob			Straight or curved lever	Straight or curved lever	Std Lever Rose Hardware Design; Choice of 4 lever designs	Std Lever Rose Hardware Design, Custom choice of 300 Grade 1 Trim lever/knob designs	Std Lever Rose Hardware Design Custom choice of 300 Grade 1 Trim lever/knob desig
5,000	35,000		40000	40000	40000	35000		40000	40000	40000	35000	35000	40000	40000	40000
00	500		500	500	500	500		500	500	500	500	500	500	500	500
Prox HID	iClass HID Prox 13.56MHz		PDL1300 for Prox HID		Prox HID	ETPDN for Prox HID		PDL1300ET for Prox		Prox HID		Prox HID	Choice of Oval or Square Multitechnology Reader, HID,iClass; Also available Mag Swipe Reader	Choice of Oval or Square Multitechnology Reader, HID,iClass; Also available Mag Swipe Reader	Choice of Oval or Square Multitechnology Reader, HID,iClass
													T Model has Bluetooth LE App - No keys, no ID + Audit trail	T Model has Bluetooth LE App - No keys, no ID + Audit trail	J Model has Bluetooth LE App - No keys, no ID + Audit trail
Global lockdown	Global lockdown					Global Lockdown					Global lockdown	Global lockdown	Global lockdown	Global lockdown	Global lockdown
													FD	CR Classroom or DB Deadbolt; FD	CR Classroom or I Deadbolt; FD
itandard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard			
landed; Field eversible	Nonhanded	Nonhanded	Nonhanded	Nonhanded.	Nonhanded.	Nonhanded.	Nonhanded	Nonhanded			Nonhanded	Nonhanded	Nonhanded	Handed; Field Reversible	Handed; Field Reversible
-5/8 to -7/8"	1-5/8 to 1-7/8″ others upon request	1-3/4″	1-3/4"	1-5/8 to 1-7/8" (others on request.)	1-5/8 to 1-7/8" (others on request.)	1-5/8 to 1-7/8" (others on request.)	1-3/4″	1-3/4″			1-5/8 to 1-7/8" others upon request	1-5/8 to 1-7/8" others upon request	1-5/8" to 1-7/8" others upon request	1-5/8" to 1-7/8" others upon request	1-5/8" to 1-7/8" others upon request
2-3/4" included)	2-3/4" (included) 2-3/8" opt.	31/32", 1-1/8", 1-1/2"	31/32", 1-1/8", 1-1/2"				31/32", 1-1/8", 1-1/2"	31/32", 1-1/8", 1-1/2"			2-3/4" (included) 2-3/8" opt.	2-3/4" (included) 2-3/8" opt.	2-3/4" (included)	2-3/4" (included)	2-3/4" (included)
Generic mortise cylinder, supplied.	Large key-in- knob, incld -or- IC Prep for Best/Falcon/ Arrow (w/o cyld.)	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4" 1-3/8" supported	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4" 1-3/8" supported	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4" 1-3/8" supported	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4" 1-3/8" supported			Large key-in- knob, incld -or- IC Prep for Best/Falcon/ Arrow (w/o cyld.)	Large key-in- knob, incld -or- IC Prep for Best/Falcon/ Arrow (w/o cyld.)	Large key-in knob, incld or IC prep for Best/Falcon/Arrow	Generic mortise cylinder supplied	Generic mortise cylinder supplied
	Yale, Medeco, Sargent, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage				Yale, Medeco, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage			Yale, Medeco, Sargent, Corbin/ Russwin, Schlage	Yale, Medeco, Sargent, Corbin/ Russwin, Schlage	Yale, Medeco, Sargent, Corbin/ Russwin, Schlage	Best/Falcon/ Arrow, Schlage (Note: must order appropiate IC Housing)	Best/Falcon/ Arrow, Schlage (Note: must order appropiate IC Housing)
es	yes			yes	yes	yes			yes	yes	yes	yes			
C cells years 00,000	4 C cells 5 years 500,000	2-3V Lithium, 100,000	2-3V Lithium, 80,000	5AA; 60000	5AA; 60000	4 C cells, 5 years/500,000	2-3V Lithium, 100,000	2-3V Lithium, 80,000			4 C cells 5 years 500,000	4 C cells 5 years 500,000	4 AA, 3 years / 100,000 (w/ Power Saver Circuit)	4 AA, 3 years / 100,000 (w/ Power Saver Circuit)	4 AA, 3 years / 100,000 (w/ Pow Saver Circuit)
Hr Fire ated UL	BHMA Grade 1 Lockset; 3hr. Fire Rated UL								UL	UL	Pending	Pending	BHMA Grade 1 Lockset; 3hr. Fire Rated UL	BHMA Grade 1 Lockset; 3hr. Fire Rated UL	BHMA Grade 1 Lockset; 3hr. Fire Rated UL
S26D, 10B	US26D, 10B	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US26D, US3, 10B	US26D, US3, 10B	US26D, US3, 10B	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US26D, 10B	US26D, 10B	Customizable; Std US26D, 10B	Customizable; Std US26D, 10B	Customizable; Std US26D, 10B