



SECURITY

VIDEO

SOLUTIONS

INTELLIGENCE



**ADSDUPIHC**  
Indoor Dome Housing



**ADSDUPIVRC**  
Vandal Resistant Indoor  
Dome Housing



## FEATURES

- Reinforced high impact design
- Vandal resistant option
- Compact, attractive design

- Four tamper-proof screws with driver bit supplied
- Ceiling, pole, roof, wall and corner mounts available

## SpeedDome® Ultra INDOOR DOME HOUSING

The SpeedDome Ultra indoor dome housing allows the SpeedDome Ultra dome to be installed indoors using the same design as found in the SpeedDome Ultra outdoor housing. It is available in standard and vandal resistant options.

The housing is made of a reinforced fiberglass high impact polycarbonate material along with a UV stabilized trim ring and top cover. The bubble assembly is affixed to the top via tamper-proof screws.

For applications where vandalism is a concern, a vandal resistant model is available which includes an aluminum sunshield cover and a high impact bubble which meets ANSI-87.1 impact safety standards. For additional protection a stainless steel bubble cage is provided.

Simply add an interface board, plug in the video cable, connect power and data, and install any SpeedDome Ultra. Diagnostic power and communications LEDs confirm proper connection and aid in troubleshooting. A variety of mounts accommodate the housing, making it easy to install.

The housing supports both the RUPTB and RUIOB dome bases (not included) and is supplied with either a choice of a clear or smoked bubble.

**tyco** / Safety Products

[www.americandynamics.net](http://www.americandynamics.net)



## AMERICAN DYNAMICS SPEEDDOME® ULTRA INDOOR DOME HOUSING

### SPECIFICATIONS

#### Model Numbers

ADSDUPIHC .....	Indoor Ultra Housing with clear bubble (f0)
ADSDUPIHS .....	Indoor Ultra Housing with smoked bubble (f1.0)
ADSDUIVRC .....	Vandal Resistant Indoor Ultra Housing with high-impact clear bubble (f0)
ADSDUIVRS .....	Vandal Resistant Indoor Ultra Housing with high-impact smoked bubble (f1.0)

#### Mechanical

ADSDUPIHC, ADSDUPIHS

Construction

Enclosure .....	Aluminum
Sun Shade, Trim Ring, Top Cover .....	UV stabilized polycarbonate
Color .....	Light gray
Height .....	321 mm (12.64 in)
Diameter .....	244 mm (9.61 in)
Bubble .....	Acrylic
Bubble Diameter .....	75.3 mm (6.93 in)
Weight	
Without Dome .....	1.6 kg (3.50 lbs)
With Dome .....	2.8 kg (6.20 lbs)
Shipping Weight of Housing .....	3.3 kg (7.30 lbs)
Mechanical Connection .....	1.5 in NPT

ADSDUIVRL, ADSDUIVRS

Construction

Enclosure .....	Aluminum
Sun Shade, Trim Ring, Top Cover .....	UV stabilized, polycarbonate
Sun Shade Cover .....	Aluminum with high gloss power coating
Color .....	Light gray
Height .....	321 mm (12.64 in)
Diameter .....	244 mm (9.61 in)
Bubble .....	High impact acrylic
Bubble Diameter .....	75.3 mm (6.93 in)
Bubble Cage .....	Stainless steel, painted flat black
Height .....	87.7 mm
Width .....	212 mm
Weight	
Without Dome .....	2.30 kg (5.10 lbs)
With Dome .....	3.50 kg (7.70 lbs)
Shipping Weight of Housing .....	4.00 kg (8.80 lbs)
Mechanical Connection .....	1.5 inch NPT

#### Environmental

Operating Temperature .....	10° to 50° C (16° to 122° F)
Humidity .....	0 to 95% RH (non-condensing)
Storage Temperature .....	20° to 65° C (-4° to 149° F)

#### Mounts and Adapters

<b>RHOSW</b> Indoor/outdoor short wall mount with end cap assembly		<b>RHOLW</b> Indoor/outdoor long wall mount with end cap assembly	
<b>RHOWPA</b> Indoor/outdoor pole strap adapter for RHOSW and RHOLW		<b>RHOWCA</b> Indoor/outdoor corner bracket adapter for RHOSW and RHOLW	
<b>ROENDC</b> Indoor/outdoor end cap assembly adapter		<b>RHOPN</b> Indoor/outdoor pendant mount	
<b>RHOTR</b> Outdoor over-the-roof mount with end cap assembly		<b>ROTRF</b> Outdoor floor adapter for RHOTR	
<b>RHIIB</b> Indoor I-beam clamp			

Product specifications and availability subject to change without notice.  
Certain product names mentioned herein may be trade names and/or registered trademarks of other companies.



VS335-01 08/03 L  
©2003 Sensormatic Electronics Corporation