

























Indoor Mounting Options

Product	Description	*Dome Compatibility	Weight	Dimensions (HxWxD)	Construction	Safety
RHIU3X3 3.5" x 3.5" Mounting Plate 	This mounting plate enables the dome to mount to a standard 3.5" x 3.5" duplex electrical box that is installed in the ceiling. The Top Hat housing/dome assembly also mounts to the structure.	✓ SpeedDome Ultra Series SpeedDome Optima	.09 kg (.2 lbs)	2 x 90 x 90 mm (.08 x 3 x 3 in)	Galvanized steel	
RHIU4X4 4" x 4" Mounting Plate 	This mounting plate enables the dome to mount to a standard 4" x 4" duplex electrical box that is installed in the ceiling. The Top Hat housing/dome assembly also mounts to the structure.	✓ SpeedDome Ultra Series SpeedDome Optima	.14 kg (.3 lbs)	2 x 105 x 105 mm (.08 x 4 x 4 in)	Galvanized steel	
RHIUCM Wall/Corner Mount 	This mounting structure attaches directly to a flat wall, inside corner, or outside corner. The Top Hat housing/dome assembly mounts to the structure for a quick and easy installation.	✓ SpeedDome Ultra Series SpeedDome Optima	1.8 kg (4.0 lbs)	With dome installed 224 x 101 x 201 mm (9 x 4 x 8 in)	Galvanized steel	UL
RHIULWM Long .6 m (24 in) Wall/Corner Mount 	This mount positions the dome away from the wall, enabling it to see over furniture, shelving, and displays. The mounting structure attaches directly to a flat wall, inside corner, or outside corner. The Top Hat housing/dome assembly also mounts to this structure.	✓ SpeedDome Ultra Series SpeedDome Optima	2.7 kg (6.0 lbs)	With dome installed 413 x 123 x 772 mm (17 x 5 x 31 in)	Painted steel	UL
RHOSW Short Wall Mount with End Cap Assembly 	This mounting structure attaches directly to a flat wall. When used with the RHOWCA corner bracket adapter or RHOWPA pole strap adapter, this short wall mount can be affixed to corners as well as poles. This mount's compact design with mounting cover hides the mounting plate to provide a clean and aesthetically pleasing appearance.	✓ SpeedDome Ultra Series SpeedDome Optima	1.3 kg (3.0 lbs)	With dome installed 366 x 218 x 282 mm (14 x 9 x 22 in)	Powder coated aluminum, ABS plastic, and fiber filled PVC	UL
RHOLW Long Wall Mount with End Cap Assembly 	This mount positions the dome away from the wall, enabling it to see over furniture, shelving, and displays. This mounting structure attaches directly to a flat wall. When used with the RHOWCA corner bracket adapter or RHOWPA pole strap adapter, this long wall mount can be affixed to corners as well as poles. This mount's compact design with mounting cover hides the mounting plate to provide a clean and aesthetically pleasing appearance.	✓ SpeedDome Ultra Series SpeedDome Optima	1.7 kg (3.9 lbs)	With dome installed 366 x 218 x 587 mm (14 x 9 x 23 in)	Powder coated aluminum, ABS plastic, and fiber filled PVC	UL
RHOWCA Corner Bracket Adapter 	This adapter bracket enables the long and short wall mounts (RHOSW and RHOLW) to affix to outside corners. Its powder coated aluminum construction ensures an extremely sturdy installation.	✓ SpeedDome Ultra Series SpeedDome Optima	.79 kg (1.75 lbs)	185 x 210 x 125 mm (7 x 8 x 5 in)	Powder coated aluminum	UL
RHOWPA Pole Strap Adapter 	This adapter bracket enables the long and short wall mounts (RHOSW and RHOLW) to affix to outside corners. This option contains stainless steel straps that can be daisy chained to accommodate any size pole. The kit also includes all the necessary mounting hardware. Its powder coated aluminum construction ensures an extremely sturdy installation.	✓ SpeedDome Ultra Series SpeedDome Optima	.5 kg (1.1 lbs)	138 x 79 x 27 mm (5 x 3 x 1 in) Straps support 53 to 951 mm (2 to 38 in) pole diameter	Powder coated aluminum and stainless steel	UL
RHSDA Ceiling Pendant Mount 	This adapter allows a SpeedDome Ultra to be retrofitted into an existing SpeedDome housing via the housing's snap-hinge mounts, making installation fast and easy. A shirt assembly is included with this SpeedDome Housing adapter kit to compensate for the smaller dimensions of the SpeedDome Ultra.	✓ SpeedDome Ultra Series SpeedDome Optima	1.4 kg (3.0 lbs)	106 x 205 x 250 mm (4 x 8 x 10 in)	Anodized aluminum	

Outdoor Mounting Options

Product	Description	*Dome Compatibility	Weight	Dimensions (HxWxD)	Construction	Safety
RHOSW Short Wall Mount with End Cap Assembly 	This mounting structure attaches directly to a flat wall. When used with the RHOWCA corner bracket adapter or RHOWPA pole strap adapter, this short wall mount can be affixed to corners as well as poles. This mount's compact design with mounting cover hides the mounting plate to provide a clean and aesthetically pleasing appearance.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	1.3 kg (3 lbs)	With dome installed 366 x 218 x 282 mm (14 x 9 x 11 in)	Powder coated aluminum, ABS plastic, and fiber filled PVC	
RHOLW Long Wall Mount with End Cap Assembly 	This mount positions the dome away from the wall, enabling it to see over awnings, soffits and landscaping. This mounting structure attaches directly to a flat wall. When used with the RHOWCA corner bracket adapter or RHOWPA pole strap adapter, this long wall mount can be affixed to corners as well as poles. This mount's compact design with mounting cover hides the mounting plate to provide a clean and aesthetically pleasing appearance.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	1.7 kg (3.9 lbs)	With dome installed 366 x 218 x 587 mm (14 x 9 x 23 in)	Powder coated aluminum, ABS plastic, and fiber filled PVC	
RHOWCA Corner Bracket Adapter 	This adapter bracket enables the long and short wall mounts (RHOSW and RHOLW) to affix to outside corners. Its powder coated aluminum construction ensures an extremely sturdy installation.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	.79 kg (1.75 lbs)	185 x 210 x 125 mm (7 x 8 x 5 in)	Powder coated aluminum	
RHOWPA Pole Strap Adapter 	This adapter bracket enables the long and short wall mounts (RHOSW and RHOLW) to affix to outside corners. This option contains stainless steel straps that can be daisy chained to accommodate any size pole. The kit also includes all the necessary mounting hardware. Its powder coated aluminum construction ensures an extremely sturdy installation.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	.5 kg (1.1 lbs)	138 x 79 x 27 mm (5 x 3 x 1 in) Straps support 53 to 951 mm (2 to 38 in) pole diameter	Powder coated aluminum and stainless steel	
RHOPN Outdoor Pendant Mount 	This mount allows an outdoor dome housing to be suspended from an outdoor ceiling or horizontal surface. It can be installed using either 1.25" NPT threaded pipe or rigid conduit, either new or existing, up to 3 meters (10 feet) in length.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	1.8 kg (4.0 lbs)	115 x 120 x 120 mm (4.5 x 5 x 5 in)	Powder coated aluminum and ABS plastic	
RHOTR Over-The-Roof Mount with End Cap Assembly 	This mount affixes directly to any vertical roof wall or parapet. This mount positions the dome away from the wall, enabling it to see over awnings, soffits and landscaping. Its opposing wing brackets ensure a secure installation to the roof surface, while allowing the pole to be repositioned for easy service access.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	5.7 kg (12.7 lbs)	1098 x 243 x 473 mm (43 x 10 x 19 in)	Powder coated aluminum, stainless steel, ABS plastic, and fiber filled PVC	
ROTRF Floor Adaptor for RHOTR 	This adapter enables the RHOTR over-the-roof mount to be installed on horizontal and vertical roof/parapet surfaces. Multiple fastening positions ensure versatility for mounting on any combination of surfaces and angles.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	2.59 kg (5.75 lbs)	369 x 240 x 240 mm (15 x 10 x 10 in)	Powder coated aluminum	
ROENDC End Cap Assembly 	This mounting assembly allows existing outdoor installations containing any SpeedDome wall, pole, corner, or over-the-roof mount to be retrofitted to accommodate newer outdoor dome/housings. The assembly's modular design allows an installer to mount the housing to the end cap on the ground, before affixing the housing/end cap assembly to the mounting pole; this ensures a safe and easy installation.	✓ SpeedDome Ultra Series ✓ SpeedDome Optima	.32 kg (.70 lbs)	64 x 103 x 194 mm (3 x 4 x 8 in)	Fiber filled PVC	