


Mounting Accessories

Mounting is simplified with Strategy Series® style "Dog Leg" tabs that allow easy installation into drop tile or drywall ceilings with provided tile bridge assembly. The tile bridge consists of two "V" shaped formed mounting rails and a C-Ring assembly. The C-Ring can be attached to the rails with the screws provided to extend support to the T-bar grid in suspended ceiling applications. Multiple hole locations are provided to allow the C-Ring to be positioned to the outer edge of the tile if necessary.

For existing dry-wall applications the tile bridge C-Ring and support rails can be inserted into the hole cut for the FAP62T. For easy positioning the "V" shaped support rails match the shape of the C-Ring tabs for easy maneuvering and location when working "blindly" above the deck. A uniquely designed "easy access" input panel on the side of the enclosure allows for "thru" conduit runs using flexible or rigid conduit. Below this cover resides a detachable Phoenix / Euro style locking four-pole connector, which provides for easy daisy chain wiring to other full range 70.7V loudspeakers or Atlas Sound FAPSUB subwoofers. The package includes an attractive press-fit grille, which nicely matches contemporary architecture.

For new construction drywall ceiling applications, the optional FAP62-TR trim ring is available. This unit provides a marked location for drywall installers to cut around essentially reserving the desired location in the ceiling until final installation of FAP62T. Mounting holes are provided to accommodate 16" or 24" OC stud / joist mounting.

A support ring is also provided on the top of the FAP62T enclosure to facilitate an auxiliary support cable. It is recommended that this secondary support be utilized in drop ceilings for safety and seismic considerations.



Architect & Engineer Specifications

The loudspeaker system shall be Atlas Sound FAP62T. System shall include a high performance 6" coaxial loudspeaker, ported bass reflex enclosure and press-fit grille for conventional ceiling installation.

Frequency response for the system shall be 63Hz – 20kHz (± 7 dB). Sensitivity shall be 88dB average.

Loudspeaker shall be comprised of a 6" coaxial cone type driver. Cone shall be constructed of polypropylene with a butyl rubber surround. The 19 mm tweeter shall be constructed of PEI. Magnet shall be a minimum of 10 oz (264g) and the voice coil diameter shall be 1" (25 mm).

Transformer shall be a 70.7V / 100V type with 2, 4, 8, 16, and 32 watt primary taps (@70.7V) with a front mounted tap selector switch to include transformer bypass setting for 8 Ω direct coupled operation.

Enclosure shall be a deep drawn steel enclosure design. Internal volume shall be 475 in³. To facilitate connection in conduit systems, enclosure shall be equipped with an access panel covering a recessed terminal cup. This cover shall provide a combination $\frac{3}{4}$ " (19mm inside diameter) / 1" (25mm inside diameter) knock-out on the side access and a top access compression fitting / strain relief to facilitate flexible conduit up to 22mm outside diameter or 1" (25mm inside diameter) conduit when the compression fitting is removed.

External wiring shall be accomplished via a removable lockable wiring connector with screw-down terminals to provide both secure wire termination and pre-wiring capability before loudspeaker installation. The 4 pole locking connector shall facilitate in/out connections and shall be located in the recessed area behind the conduit access panel.

Seismic support eye shall be provided on top of enclosure for additional suspension point when used in drop tile ceilings. Construction of enclosure shall be a minimum of 18-gauge deep drawn galvanized metal.

The system shall include a support backing plate to reinforce the ceiling material and tile support rails for use on either 2' x 4' (609mm x 1219mm) or 2' x 2' (609mm x 609mm) suspended ceiling tiles. This assembly can all be installed from beneath the ceiling tile.

Overall front face diameter shall not exceed 12 $\frac{1}{2}$ " (318mm); overall depth from the bottom of the ceiling shall not exceed 8.48" (215mm).

Grilles shall be press-fit, manufactured from 24-gauge perforated steel mesh and finished in white epoxy. Round grill shall be 10.48" (266mm) diameter.

The loudspeaker shall be the Atlas Sound FAP62T.