



HARDENED



FLEXIBILITY



UPLINKS



2




4



30W[†]



60W[†]



The ComNet™ CNGE2FE4SMS[POE][HO] is a six-port self-managed switch with uplink management functionality and provides 4 copper ports operating at 10/100 Mbps and two Gbps optical SFP* ports. It is designed to combine four electrical ports and one Gbps SFP port into one of two optical SFP ports. The CNGE2FE4SMS[POE][HO] SFP ports forwards this data to the next network device or can be configured for drop and insert operation. The CNGE2FE4SMS[POE][HO] uses ComNet SFPs for connector and distance options. There is no programming required to use this product. The ComNet CNGE2FE4SMS[POE][HO] comes pre-programmed, preventing network video flooding with dip switch selection of fiber ports as uplink or as an unmanaged switch. Ports 1 to 4 can supply up to thirty (30) watts of power ("Power over Ethernet") per port based on the IEEE 802.3at standard. An optional High Output (HO) version is also available that can supply up to thirty (30) watts of PoE from ports 1 and 2 and up to sixty (60) watts of PoE from ports 3 and 4.

FEATURES

- › No Programming Required
- › 10/100/1000 Mbps Ethernet
 - 10/100 BASE-T/TX electrical ports
 - 1000 BASE-FX SFP ports for Gigabit operation
- › Electrical ports support Auto-Negotiation for 10 Mbps or 100 Mbps, full duplex or half duplex data.
- › Optical port supports 1000 Mbps full duplex data
- › IEEE802.3at Power over Ethernet (PoE+)[†]
- › Up to 30 W PoE+ on Ports 1 and 2[†]
Up to 60 W PoE+ on Ports 3 and 4[†]
- › Automatic MDI/MDI-X crossover
- › Designed to meet full compliance with the environmental requirements (ambient operating temperature, mechanical shock, vibration, humidity with condensation, high-line/low-line voltage conditions and transient voltage protection) of NEMA TS-1/TS-2 and the Caltrans Specification for Traffic Signal Control Equipment.

- › Voltage transient protection on all power and signal input/output lines provides protection from power surges and other voltage transient events.
- › No in-field optical adjustments required
- › Power, Activity and Port PoE status LED indicators confirm operating status of this device
- › Hot-swappable rack modules
- › IEEE 802.3 compliant
- › Lifetime Warranty

APPLICATIONS

- › 10/100/1000 Mbps Ethernet
- › High Speed Computer Links
- › IP Video

* SFP = Small Form-Factor Pluggable Module

[†] CNGE2FE4SMSPOE or CNGE2FE4SMSPOEHO models only

CNGE2FE4SMS[POE][HO]

10/100/1000 Mbps Drop/Insert/Repeat
Gigabit Uplink Switch with Optional PoE+

SPECIFICATIONS

Data		LED Indicators	
Data Interface	Ethernet	- Optical Link/Data Activity	
Data Rate	10/100/1000 Mbps	- Electrical Link/Data Activity	
	IEEE 802.3 Compliant	- Power - PoE	
	Full Duplex or Half Duplex Electrical Ports/Full Duplex Optical Port		
Electrical	CNGE2FE4SMSPOE Ports 1 – 4: 30 W Max		
	CNGE2FE4SMSPOEHO Ports 1 and 2: 30 W Max		
	CNGE2FE4SMSPOEHO Ports 3 and 4: 60 W Max		
Fibers ¹ Connectors		Power	
Optical	Requires selection of sold-separately SFP modules. See ComNet data sheet for number and description of SFP modules.	Operating Voltage	48 to 57 VDC PoE, 12 to 24 VDC non-PoE
		Current Draw	5A max, with PoE, 1A w/out PoE
Power Data	Terminal Block	Electrical & Mechanical	
	RJ45	Surface Mount	Wall or Flat Surface Screw Attachment
POE Pin Assignment		Current Protection	Automatic Resettable Solid-State Current Limiters
	RJ45 port supports IEEE802.3at	Circuit Board	Meets IPC Standard
	End-point Positive (VCC+): RJ45 pin 1, 2	Size	6.1 × 5.3 × 1.1 in (15.5 × 13.5 × 2.8 cm)
	(RJ45 pin 1,2 and 4,5 on 60W ports)	Shipping Weight	<2 lbs./0.9 kg
	Negative (VCC-): RJ45 pin 3, 6	Environmental	
	(RJ45 pin 3,6 and 7,8 on 60W ports)	MTBF	>100,000 hours
		Operating Temp	-40° C to +75° C
		Storage Temp	-40° C to +85° C
		Relative Humidity	0% to 95% (non-condensing) ¹

AGENCY COMPLIANCE

FC

CE

UL

US

RoHS

REACH

WEEE

PART 15 COMPLIANT

E322911

124621


MADE IN THE USA

ORDERING INFORMATION

Part Number	Description
CNGE2FE4SMS	6 Port Gigabit and 10/100 Mbps Ethernet Self-managed Switch 2 SFP FX, 4TX
CNGE2FE4SMSPOE	6 Port Gigabit and 10/100 Mbps Ethernet Self-managed Switch 2 SFP FX, 4TX with 30W of PoE+ power
CNGE2FE4SMSPOEHO	6 Port Gigabit and 10/100 Mbps Ethernet Self-managed Switch, 2 SFP FX, 2TX with 60W of PoE+ power, 2TX with 30W of PoE+ power
Included Accessories	DC Plug-in Power Supply, 90-264 VAC, 50-60 Hz (included with CNGE2FE4SMS only)
Options	Power Supply for PoE Models (Extra charge, order model PS48VDC-5ADIN) [1] Add suffix 'C' for Conformally Coated Circuit Boards to extend to condensation conditions (Extra charge, consult factory) DIN-Rail Mounting Adaptor Plate Kit - With mounting hardware (Optional, order model DINBKT1 or DINBKT4)

NOTE: This product requires a fiber installation with a minimum 30 dB connector return loss. The use of Super Polish Connectors is recommended.
Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J. In a continuing effort to improve and advance technology, product specifications are subject to change without notice.

TYPICAL APPLICATION



Low Power Consumption