



## CSGL7-06B2

Compact SureGround™ Grounding Kit for 1-5/8 in corrugated coaxial cable

**OBSOLETE**  
Replaced By

CSGL7-06B2-T

Compact SureGround™ Grounding Kit for 1-5/8 in corrugated coaxial cable

### Dimensions

Nominal Size	1-5/8 in
Bonding Conductor Length	609.6 mm   24 in
Cable Jacketing Removal Length, maximum	59.1 mm   2.3 in
Cable Jacketing Removal Length, minimum	55.9 mm   2.2 in
Compatible Diameter, maximum	50.800 mm   2.000 in
Compatible Diameter, minimum	49.022 mm   1.930 in
Enclosure Length	80.0 mm   3.2 in
Enclosure Width	69.9 mm   2 3/4 in

### Electrical Specifications

Current Handling	Tested to withstand 100,000 amps peak current surge
Current Handling Test Method	MIL-STD-1757
Grounding, Bonding and Shielding Test Method	MIL-STD-188-124A
Lightning Protection Test Method	IEC 1024-1

### General Specifications

Cable Type	Corrugated
Grounding Kit Type	Compact SureGround™ Grounding Kits
Ordering Note	CommScope® non-standard product
Color	Black
Bonding Conductor Material	Copper
Bonding Conductor Wire Size	16 mm <sup>2</sup>
Bonding Conductor Jacketing Material	PVC
Grounding Strap Material	Copper
Includes	Grounding kit   Hardware   Lug
Locking Bail Material	Stainless steel
Lug Attachment	Factory attached
Lug Type	Two-hole lug
Package Quantity	1
Rivet Material	Copper
Weatherproofing Method	Copper strap contact overmolded with EPDM rubber

CSGL7-06B2

## Mechanical Specifications

Blowing Rain Test Method	MIL-STD-810, Method 506
Corrosion Test Method	MIL-STD-1344, Method 1001
Freezing Rain/Icing Test Method	MIL-STD-810, Method 521
Humidity Test Method	MIL-STD-1344, Method 1002
Immersion Test Method	IEC 60529:2001, IP68
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Thread Size	3/8 in
UV Resistance Test Method	MIL-STD-810, Method 505
Vibration Test Method	MIL-STD-202, Method 214

## Packed Dimensions

Height	203.2 mm   8.0 in
Length	76.2 mm   3.0 in
Shipping Weight	0.50 kg   1.10 lb
Width	127.0 mm   5.0 in

## \* Footnotes

Grounding, Bonding and Shielding Test Method	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
Lightning Protection Test Method	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02