

SC60 Series surface door closers

- Light-medium duty door closer
- Adjustable sizes 1-5
- ANSI/BHMA 156.4, Grade 1 certified
- Meets ANSI 117.1
- Closers without Hold-Open arms are UL 10C fire rated.



SC60 Series	Arm function	Finish	Handing	Cylinder assembly	Cover	SKU
SC61	Rw/PA	ALUM	-	Std	Less	43571
SC61	Rw/PA	DKBRZ	-	Std	Less	43573
SC61	Hw/PA	ALUM	-	Std	Less	43583
SC61	Rw/PA	ALUM	-	Std	Slim	43601

Note: All SC60 Series closers ship with thru bolt, wood and machine screws (TBWMS).

SC70 Series surface door closers

- Heavy duty door closer
- Adjustable sizes 1-6
- ANSI/BHMA 156.4, Grade 1 certified
- Meets ANSI 117.1
- Closers without Hold-Open arms are UL 10C fire rated.



SC70 Series	Arm Function	Finish	Handing	Cylinder assembly	Cover	SKU
SC71	Rw/PA	ALUM	-	Std	Full	43002
SC71	Rw/PA	DKBRZ	-	Std	Full	43003
SC71	Hw/PA	ALUM	-	Std	Full	43108
SC71	HD/PA	ALUM	-	Std	Full	43008
SC71	DS	ALUM	-	Std	Full	43014
SC71	DS/HO	ALUM	-	Std	Full	43020

Note: All SC70 Series closers ship with thru bolt, wood and machine screws (TBWMS).

SC80 Series surface door closers

- Medium duty door closer
- Adjustable sizes 1-6
- ANSI/BHMA 156.4, Grade 1 certified
- Meets ANSI 117.1
- Closers without Hold-Open arms are UL 10C fire rated.



SC80 Series	Arm Function	Finish	Handing	Cylinder assembly	Cover	SKU
SC81	Rw/PA	ALUM	-	Std	Slim	43420
SC81	Rw/PA	DKBRZ	-	Std	Slim	43476
SC81	Rw/PA	ALUM	-	Std	Full	43434
SC81	Rw/PA	DKBRZ	-	Std	Full	43490
SC81	DS	ALUM	-	Std	Slim	43416
SC81	Hw/PA	ALUM	-	Std	Slim	43419
SC81	Hw/PA	DKBRZ	-	Std	Slim	43475
SC81	Hw/PA	ALUM	-	Std	Full	43433
SC81	Hw/PA	DKBRZ	-	Std	Full	43489

Note: All SC80 Series closers ship with thru bolt, wood and machine screws (TBWMS).

SC90 Series surface door closers

- Light duty door closer
- Fixed sizes; Size 4 available
- ANSI/BHMA 156.4, Grade 3 certified
- Closers without Hold-Open arms are UL 10C fire rated.

SC90 Series	Arm Function	Finish	Handing	Cylinder assembly	Cover	SKU
SC94	Rw/PA	ALUM	-	Std	Less	41891
SC94	Rw/PA	DKBRZ	-	Std	Less	41942

Note: All SC90 Series closers ship with thru bolt, wood and machine screws (TBWMS).

Notes: **ALUM** = Aluminum painted finish (689); **DKBRZ** = Dark bronze finish (695)

Rw/PA = Regular arm with parallel arm bracket

Hw/PA = Hold open arm with parallel arm bracket (Please note hold open arm configurations are not UL listed.)

DS = Dead stop arm

DS/HO = Dead stop hold open arm (Please note hold open arm configurations are not UL10C listed.)