
Features:

- 8 inch pulp fiber full range dual woofer cone
- 5.4 oz ferrite woofer magnet
- 5 watt 25/70 volt transformer
- Four wattage taps
- 16 gauge steel pure white enamel grille
- 4 universal white mounting screws
- Optional square surface mount back box (SQ-BB)
- Optional T-Bar support brackets (T-BAR)
- 3 year warranty



Specifications:

- Speaker Type – Dual cone
- Cone Material – Pulp fiber
- Frequency Response – 50Hz – 15kHz (+/- 4dB)
- Sensitivity – 92dB 1W 1M
- Dispersion – 96 degrees
- Impedance – 8 ohms nominal
- Power handling – 20 watts-peak
- Magnet type – Ferrite
- Magnet weight – 5.4 oz / 153g
- Voice coil diameter – 0.75" / 19mm
- Flux density – 11,600 gauss
- Speaker depth – 2.76" / 70mm

Transformer:

- Primary voltage – 25/70-volt
- Primary taps – 0.625 / 1.25 / 2.5 / 5 watts
- Secondary tap – 8 ohms
- Frequency response – 80Hz – 15 kHz (+/- 5dB)
- Insertion loss - 0.5dB

Baffle:

- Construction – Steel
- Finish – Pure white enamel
- Baffle Mounting – 11" / 294mm lateral centers
- Dimensions:
 - L – 12.5" / 318mm
 - W – 12.5" / 318mm
 - D – 0.2" / 5mm
- Total weight - 3.75 lbs (1.70kg)
- Master carton – 6 pcs