

Grade 2 Cylindrical Lever / Knob Locksets

APPLICATIONS:

Heavy-duty commercial lockset suitable for interior and exterior doors of schools, universities, medical and office buildings, hotel / motel, public buildings, and religious, multi-family, retail, and government facilities.



STANDARD FEATURES:

CERTIFICATIONS: ANSI A156.2 Grade 2, UL Listed 3-hr, ADA and title 19 California Fire Marshal.



MECHANISM: cold-rolled steel chassis housing reversible & non-handed lever available clutched or rigid with separate lever spring mechanism to prevent sagging and droop

DOOR THICKNESS: 1-3/8" to 1-3/4"

BACKSET: 2-3/4"

STRIKE: 1-1/4" x 4-7/8", ANSI strike, square corner

LATCH: 2-1/4" x 1-1/8", square corner face plate, 1/2" throw, UL Listed 3-hr

THROUGH-BOLTS: Removeable through-bolts, (Without through-bolts, the lock is NOT Grade 2 compliant)

CYLINDER: Drilled 6, pinned 6 solid brass cylinder with Schlage keyway, keyed differently, 2 cut keys

SFIC CORE: Prepped for either 6-pin or 7-pin SFIC core.

TRIM: 3-5/16" rose diameter for "S" style lever, lever return is 3/8" from door, "P" and "B" knob styles

CASE QTY: Levers 6, Knobs 20

FUNCTIONS:

ANSI CODE

10 - PASSAGE SET

F75

Latch bolt operated by knob/lever, from either side at all times.



40 - PRIVACY LOCK

F76

Latch bolt operated by knob/lever from either side. Outside knob/lever is locked by push button or other locking device inside and unlocked by emergency release outside, operating inside knob/lever or closing door.



53 - ENTRANCE LOCK

F109

Dead locking latch bolt operated by knob/lever from either side except when outside knob/lever is locked by the push or turn button inside. Key outside or operating inside knob/lever releases push or turn button unlocking outside knob/lever except when push or turn button has been rotated to keep outside knob/lever locked. Inside push or turn button must be manually operated to unlock outside knob/lever. Inside knob/lever always operates latch bolt.



70 - CLASSROOM LOCK

F84

Dead locking latch bolt operated by knob/lever from either side except when outside knob/lever is locked from outside by key. Inside knob/lever always operative.



80 - STOREROOM LOCK

F86

Dead locking latch bolt operated by key in outside knob/lever, or by operating inside knob/lever. Outside knob/lever is always inoperable.



GENERAL LOCK


Quality & Value™

— Product Guide 105.0 — Ab:1

Grade 2 Cylindrical Lever / Knob Locksets

How to Order - Nomenclature

L X 2 53 S 626 C 234 S ANSI




Note: No all functions are available in all trim styles, finishes, latch/strike and cylinder options.

Grade 2 Latches

How to Order - Nomenclature

2 SL 605 234 R



Grade 2 Cylindrical Components

COMPONENTS:

Springlatch	Part #	Finish
2-3/4" radius-corner springlatch	2SL xxx 234 R	Specify
2-3/8" radius-corner springlatch	2SL xxx 238 R	Specify
2-3/4" square-corner springlatch	2SL xxx 234 S	Specify
2-3/8" square-corner springlatch	2SL xxx 238 S	Specify
2-3/4" drive-in springlatch	2SL 234 D	n/a
2-3/8" drive-in springlatch	2SL 238 D	n/a
Deadlatch		
2-3/4" radius-corner deadlatch	2DL xxx 234 R	Specify
2-3/8" radius-corner deadlatch	2DL xxx 238 R	Specify
2-3/4" square-corner deadlatch	2DL xxx 234 S	Specify
2-3/8" square-corner deadlatch	2DL xxx 238 S	Specify
2-3/4" drive-in deadlatch	2DL 234 D	n/a
2-3/8" drive-in deadlatch	2DL 238 D	n/a
Extension Link		
5" deadlatch extension for use with Grade two 2-3/8" backset	2DL Ext	
3-3/4" deadlatch extension for use with Grade two 2-3/8" backset	2DL Ext	
Tailpiece		
Grade 2 Lever IC Tailpiece	L2 IC TP 2	

GENERAL LOCK

Quality & Value™

— Product Guide 105.0 — Ab:3