

IN-162POEWM

16 - Port PoE Switch with Gigabit Uplink



Features

- ✖ Two-layer network management PoE switch
- ✖ Supports IEEE802.3af, IEEE802.3at standards
- ✖ Conform IEEE802.3, IEEE802.3u, IEEE802.3ab and IEEE802.3X standards
- ✖ Supports “One Key Recovery” of IP address and user password

Technical Specifications

System	
Ethernet Port	2*10/100/1000 Base-T; 16*10/100 Base-T(PoE power supply)
PoE Power consumption	Each power ≤30W; Total≤250W
PoE Protocol	IEEE802.3af IEEE802.3at
PoE Budget	250W
Switching Capacity	24.8G
Packet Forwarding Rate	5.36Mpps
Application Humidity	10%-90%
Power	AC 100~240V
Lightning Protection	Common Mode 2KV Differential Mode 1KV
Working Temperature	-10°C~55°C
Weight	2.69kg
Dimension(W×D×H)	442mm×124mm×44.5mm