

TABLE OF CONTENTS

General Information.....	2	Accessories / Options (continued) .....	6-9
Patents.....	2	21BSH shroud option .....	7
11B Series .....	3	Cables.....	7
21B Series .....	4	Special stamps.....	8
41B Series .....	5	Frangible shackle option .....	8
Accessories / Options .....	6-9	Chain options.....	8
Car seal option .....	6	Lockout/Tagout .....	9
Weather cover option.....	6	Patented keying system.....	10
Double lockout "safety first" option.....	6	Repair and parts.....	11

GENERAL INFORMATION

At the heart of every Stanley/Best padlock is a standard key removable core that is interchangeable throughout most of the entire line of BEST® products. This standardization permits Stanley/BEST locks of any type, size or style to be masterkeyed into one system which can expand to include future locking needs.

All padlocks utilize the interchangeable core which allows immediate rekeying at minimal cost. Padlocks are available in various case sizes and brass or stainless steel shackle sizes (see chart below). Brass cases with brass shackles are also available. Options include key retained / non-key retained, bronze or steel chains, special case embossing (Brass case only), corrosion resistance, car seal. See pages 6-9 for a complete list of options available.

PATENTS

Products protected by one or more of the following patents:

3,603,123	4,075,878	3,882,699	3,850,014
3,652,114	3,728,879	3,605,458	4,244,093
4,386,510	4,424,693	4,444,034	4,655,063
D290,085	5,590,555	5,794,472	



Specifications

**Case** – Machined from solid extruded brass.  
Standard finish is 626 satin chromium plated.  
**Width** – 1 5/8"  
**Length** – 2 1/16"  
**Thickness** – 25/32"

**Shackle** – The shackle locks at both heel and toe.  
The length of shackle opening is measured from top of case to inside of shackle when padlock is locked.

**Material** – Brass or stainless steel  
**Diameter** – 1/4"  
**Width of opening** – 1/8"


**ASTM F883** – Meets Grade 3 with stainless steel shackle.  
**ASTM F883** – Meets Grade 6 for option E. (Corrosion resistance).



11B Padlock




11B72 Actual Size



11B722 Actual Size



11B772 Actual Size



11B782 Actual Size

11B – HOW TO ORDER

11B	7	2	T	626		
Series	Core Housing	Shackle Height	Function Code	Chain Option	Special Stamp No.	Options
11B – brass 1/4" diameter	7 – 7 pin housing accepts all BEST® cores	Steel 2 – 3/4" 22 – 1 1/2" 72 – 2" 82 – 4" Brass 0 – 3/4" 20 – 1 1/2" 70 – 2" 80 – 4"	T – key retained L – non-key retained	M – case drilled for clevis only M1* – bronze chain (available for brass padlocks only) M5* – galvanized steel chain  (page 8)	Blank – BEST® logo PS1010 – safety first  Specify padlock stamp number or describe stamp.  Price for special stamps on request.  (page 8)	F3 – frangible shackle (11B720 only) 606 – satin brass ZZ – double lockout  (page 8)

## ACCESSORIES AND OPTIONS

### Special Stamped Padlocks

Upon special request, and at no charge other than the initial cost of the die, Stanley/BEST padlocks may be die-stamped with the customer's identification as specified. If stamp has been previously ordered, specify stamp number. (Brass padlocks only.)



Samples of Padlock Stamping

### F3— Option Frangible Shackle

Available in 11B series only. The frangible shackle padlock is designed for fire and safety equipment, cabinets, etc. where casual entry needs to be prevented. During emergency, the shackle may be snapped by a hard blow or strong, steady pressure permitting entry without use of a key. (Check lock regulations). A brass 1 1/2" – number 20 size shackle is made frangible through use of special break point. Broken shackles are easily replaced in the field and may be ordered separately. A complete frangible shackle kit (including three frangible shackles, three shackle springs and one padlock disassembly tool) may be ordered with each padlock order.

To order kit specify: **11BFK**



Frangible Shackle Kit

### M-Option Chains

Chains may be supplied with padlock. When ordering clevis and chains, add M1 or M5 to padlock nomenclature. Standard chain length is 9", special length chains available upon request.



M1 – 9"  
Bronze Chain

M5 – 9"  
Galvanized Steel Chain with Gray  
Plastic Polycoat Cover