


Simplex® 2015



2015



- Combination Entry
- Egress with Exit Device (not supplied)
- Compatible with Many Rim Mounted Exit Devices
- Exterior Combination Change (only)

Features

Access Control

Mechanical pushbutton lock eliminates problems and costs associated with issuing, controlling, and collecting keys and cards. Provides exterior access by combination, while allowing free egress at all times by interior Exit Device (not supplied).

No Battery

Fully mechanical lock eliminates the material and labor expense of battery replacements

Locking Device Options

Rim Exit Device: Compatible with most leading brands of Exit Devices (Exit Device and mounting hardware not included)

Exit Device Compatibility

See list of compatible devices on reverse.

Number of Codes

Single access code—one easy-to-manage code for all users

Programming

Lock is easily programmed via keypad without removing lock from the door

Handing

For non-handed or clockwise-rotating (adjustable up to 90°) Exit Device hubs only

Operation Modes

Pushbutton Access, Exit Device may be "dogged" without affecting the 2015

Economical

A cost effective access control solution

Tailpiece

2¾" (70 mm) adjustable tailpiece for Exit Device operation from outside; Optional 5" (127 mm) tailpiece available (sold separately; part # 74773-000-001)

Exit Device Hub Rotation

Adjustable up to 90° clockwise for right hand (adjustable cam)

Mechanical Features

Construction	Heavy-duty, cast front housing
Numeric Keypad	Vandal resistant, solid metal pushbuttons
Door Handing	For non-handed or clockwise-rotating (adjustable up to 90°) Exit Device hubs only
Finishes	Satin Chrome 26D (626)
Control	6-pin tumbler cylinder keys for combination change access; keyed differently; optional keyed alike or master keyed
Latch	Not supplied (see compatibility list below)
Strike	Not supplied (supplied with Exit Device)
Minimum Stile Recommended	3 1/8" (79 mm)
Weight	3.5 lbs. (1.6 kg)

Installation

Door Preparation	Exit Device preparation may require recessed through bolting; 2015 installation is based on centerline of mating Exit Device hub
Door Thickness	1 3/8" (35 mm) to 2 1/2" (64 mm); optional 5" (127 mm) tailpiece (purchased separately)
Items Supplied Include	Installation manual, full-scale template, combination change keys, and required lock installation hardware only

Certification and Testing

Durability	Weather resistant
------------	-------------------

Warranty

Warranty	1-year warranty
----------	-----------------

Compatible Exit Devices

American Device 6300 Series, 6303 Series

Corbin 21, 22, 25, 26NT, 27K, 29, 29-1/4, 29M2, 29-1/2M2, 29NTM2, 29D20, LA29, 39, 39EL, 39LLD, 390, LA39

Detex Advantex Series 10, 20, 21, 40, 50, 51

Dorex 8500R/8500F

Dorex 9500R/9500FR

Magno Krom LHR only: 500-4, 550-4, 650-4, 1500-4, 1550-4, 1650-4; RHR only: 600-3

Monarch 18RBA, 18RP, 18VP, F18RBA, F18RP, F18VP, FXXRBA, FXXRP, FXXVP, XXRBA, XXRP, XXVP

Precision Hardware FL-D103; RHRB only 810-H;

RH or LH: 103, R103, D203, H-203, 1103, D1203, H1203

Russwin 365, 3651/4, LT365, 370, 372, LA372, 375, LT375, 377, 382, 384, 385, 388, 572, 572EL, 572ELD, U572, LA572

Sargent 2813, 2804, 6804, 12-6804, 9804RHRB, 12-9804LHRB, 9898E, 9898K

Von Duprin 22 Rim, 22 Rim-F, 88 Rim, 88 Rim-F, 98 Rim, 98 Rim-F, 99 Rim, 99 Rim-F; 2227, 2227-F, 9827, 9827-F, 9847, 9847-F, 9927-F, 9947-F

Yale 1500 Series, 7000 Series

Cannot be used with surface-mounted Exit Devices with counterclockwise rotating hubs, thumb-operated Mortise design Exit Devices, or vertical rod Exit Devices

Attention: compatibility is subject to change if modifications are made by Exit Device manufacturers without Kaba's knowledge

