



innovation and inspiration

Thanks to state-of-the-art engineering and innovative thinking, the 5300LN is truly a source of inspiration. With three lever designs and a choice of thirteen different finishes, you have the freedom and ability to match any décor.

But looks aren't everything. This revolutionary Grade 2 cylindrical lockset boasts design features such as a vandal-resistant Free Wheeling lever mechanism and adjustable door thickness (Patent #6,131,970) that makes installation a breeze. Through-bolting gives the 5300LN a secure fit that resists shaking and rattling. And with a lifetime warranty against lever sag, you never have to worry about your pleasing aesthetics becoming a displeasing eyesore.

A.D.A.

The 5300LN meets accessibility guidelines of the Americans with Disabilities Act and the requirements of the Uniform Federal Accessibility Standards and ANSI 117.1, all requiring ease of accessibility for the handicapped.

door thickness

Patented (patent no. 6,131,970) door adjustable rose support plates allow the 5300LN to easily adjust to doors from 1-3/4" (44mm) to 2" (51mm) thick. For 1-3/8" (35mm) or 2-1/4" (57mm) thick doors, please specify door thickness on order.

installation

5300LN series cylindrical locks conform to ANSI/BHMA Specifications A156.115 which cover hardware preparations for steel doors and steel frames and A156.115-W which cover hardware preparations for wood doors with wood or steel frames.

ISO 9001

Designed and manufactured under a certified ISO 9001 quality system.

ANSI/BHMA

Certified ANSI/BHMA A156.2, Series 4000 Grade 2.



free wheeling lever trim

All 5300LN

functions

feature

the Free

Wheeling lever mechanism. When the outside lever is locked, it will rotate freely up and down while remaining securely locked.



microshield®

5300LN series locks are available with *MicroShield* antimicrobial coating. *MicroShield* is a revolutionary hardware finish coating, using a silver ion based technology, which inhibits the growth of bacteria, algae, yeast, fungus, mold and mildew. *MicroShield* is non-toxic and lasts for the lifetime of the finish to which it is applied. To order, suffix option code "YMS". Available for 626 finish, additional finishes by special application. Contact factory for availability.



Note: *MicroShield* coating may vary finish color from architectural standards. *MicroShield* is not intended as a substitute for traditional infection control programs such as hand hygiene or use of disinfectants. Coated products must still be cleaned to insure the surfaces will be free of destructive microbes. Yale makes no representations or warranties, express or implied, as to the efficacy of *MicroShield*.

contents

Introduction	2
Features	3
Lever Designs.....	4
Functions	5-7
SecureX®	8
SecureX® Accessories	9
Cylinders	10-11
Latchbolts	12
Strikes	13
Ordering Information.....	14
Sample Specification	15

fire listings

All functions are UL - cUL Fire Listed for use on fire doors having a rating up to and including 3 hours.

Note: Any retrofit or other field modification to a fire rated opening can potentially impact the fire rating of the opening, and Yale Locks & Hardware makes no representations or warranties concerning what such impact may be in any specific situation. When retrofitting any portion of an existing fire rated opening, or specifying and installing a new fire-rated opening, please consult with a code specialist or local code official (Authority Having Jurisdiction) to ensure compliance with all applicable codes and ratings.

finishes


ANSI/BHMA Code	Finish Description
605	Bright Brass, Clear Coated
606	Satin Brass, Clear Coated
609	Satin Brass, Blackened, Satin Relieved, Clear Coated
612	Satin Bronze, Clear Coated
613	Dark Oxidized Satin Bronze, Oil Rubbed ¹
613E	Dark Oxidized Satin Bronze - equivalent
616	Satin Bronze, Blackened, Satin Relieved, Clear Coated
619	Satin Nickel Plated, Clear Coated
620	Satin Nickel Plated, Blackened, Satin Relieved, Clear Coated
625	Bright Chrome Plated
626	Satin Chrome Plated 
693	Black Powder Coat
722	Black Oxidized Bronze, Oil Rubbed ²

1. New May 1, 2010
2. Formerly 613 prior to May 1, 2010

lever designs


Augusta AU

Lever: Cast Zinc
Rose: Cold Forged Brass, Bronze




Monroe MO

Lever: Cast Zinc
Rose: Cold Forged Brass, Bronze



Pacific Beach PB







Lever: Cast Zinc
Rose: Cold Forged Brass, Bronze



See page 10 & 11 to order interchangeable core cylinder.
Dimensions are in inches (millimeters).

5300LN series | cylindrical lever locks

functions

<p>5301LN (F75)</p> <p>Passage or Closet Latch</p> <ul style="list-style-type: none"> For doors that do not require locking. Either knob operates latchbolt at all times.  <p>Outside Inside</p>	<p>5302LN (F76A)</p> <p>Privacy, Bedroom or Bath Lock</p> <ul style="list-style-type: none"> For lavatory or other privacy doors. Either lever operates latchbolt unless outside lever is locked by pushbutton inside.* Button automatically releases when inside lever is turned or door is closed. Emergency release in outside lever. Emergency key supplied. (P/N 14-5302-1053) Inside lever always active.  <p>Outside Inside</p>	<p>5303LN (F77A)</p> <p>Patio or Privacy Lock</p> <ul style="list-style-type: none"> For exit doors with limited entry. Deadlocking latchbolt. Either lever operates latchbolt unless outside lever is locked by pushbutton inside.* Button automatically releases when inside lever is turned or door is closed. Inside lever always active.  <p>Outside Inside</p>
<p>5304LN (F82A)</p> <p>Entry Lock</p> <ul style="list-style-type: none"> For entrance or office doors. Deadlocking latchbolt. Either lever operates latchbolt (except when outside lever is locked from inside).* Pushing button in inside lever locks outside lever. (Automatically releases when inside lever is turned or key is rotated in locked outside lever.) Latchbolt is operated by key in outside lever or by rotating inside lever. Inside lever always active.  <p>Outside Inside</p>	<p>5305LN (F86)</p> <p>Storeroom or Closet Lock</p> <ul style="list-style-type: none"> For use on storeroom, utility, exit doors. Deadlocking latchbolt. Latchbolt operated by lever inside, key in outside lever. Outside lever always locked.*  <p>Outside Inside</p>	<p>5306LN (F92)</p> <p>Service Station Lock</p> <ul style="list-style-type: none"> Deadlocking latchbolt. Either lever operates latchbolt. Pushbutton in inside lever locks outside lever. (Automatically releases when inside lever is turned, door is closed or key is rotated in outside lever, except when slotted pushbutton is rotated 90° clockwise to retain outside lever in locked position).* Latchbolt operated by key in outside lever, inside lever always active.  <p>Outside Inside</p>

*Lever handles are Free Wheeling in locked position. Shaded area denotes Free Wheeling lever.