



660 Series

The strongest surface mounted, multi-purpose locking solution

The 660 multi-purpose locking solution brings electronic access control to your cabinets and drawers. This electro-mechanical lock has over 1000 lbs of holding force. Strong, convenient and flexible, it is ideal for corporate and government applications including lockers, cabinets, and display cases.

Standard Features

- Static strength 1,000 lbs.
- Dynamic strength over 100 ft-lbs.
- Endurance over 1,000,000 cycles
- Available in either 12 or 24 VDC
- All metal construction
- Adjustable mounting brackets with final lockdown feature
- 6 foot cable lead
- Patents: 8,562,040; 7,878,560
- RoHS compliant
- 3-year limited warranty

Electrical

- Available in either 12 or 24 VDC
- 12 - 24 VDC +/- 10%
 - » 240 mA at 12 VDC (continuous duty)
 - » 120 mA at 24 VDC (continuous duty)
 - » 700 mA at 12 VDC (pre-load option)
 - » 350 mA at 24 VDC (pre-load option)

Optional Features

- LBSM » "Locked State" Monitoring
- Pre-load version (up to 15 lbs.)

Accessories

- KO » 660 Key override option

