



Purchase

APC



Overview

Description	APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Model Name	Rack PDU 2G, Metered, ZeroU, 17.3kW, 240V, (30) C13 & (12) C19
Includes	Installation guide , Rack Mounting brackets , Safety guide , Serial configuration cable
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Output

Nominal Output Voltage	240V
Maximum Total Current Draw per Phase	24 A
Output Connections	(30) IEC 320 C13 (Battery Backup) , (12) IEC 320 C19 (Battery Backup)
Overload Protection	Yes

Input

Nominal Input Voltage	400V 3PH
Input Frequency	50/60 Hz

Regulatory Derated Input Current (North America)	24 A
Input Connections	IEC 309 30A 3P+N+E
Cord Length	1.83 meters
Number of Power Cords	1
Maximum Line Current per phase	30 A
Maximum Input Current per phase	30 A
Load Capacity	17300 VA

Physical

Net Weight	9.6 kg
Maximum Height	1829 mm
Maximum Width	56 mm
Maximum Depth	51 mm
Shipping Weight	13.6 kg
Shipping Height	2149 mm
Shipping Width	221 mm
Shipping Depth	112 mm
Color	Black

Environmental

Operating Environment	0 - 55 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CUL Listed , EN 55022 Class A , EN 55024 , EN 61000-3-2 , EN 61000-3-3 , FCC Part 15 Class A , ICES-003 , UL Listed , VCCI Class A
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Battery Notes	Battery Notes