



WALL MOUNT ENCLOSURES

300 SERIES

SWING-OUT W/FIXED SIDE PANELS

NEW SIZES

300 Swing-Out Design Series

	300 Series	Standard Depth	Extended Depth
External Rack Size Height	15" (7U)	37.5" (20U)	51.5" (28U)
	18.5" (9U)		
	22" (11U)		
	27" (14U)		
	30.5" (16U)		
External Rack Size Width	20.5"	20.5"	
External Rack Size Depth	23.5"	30.5"	
Mounting Format (Internal)	19"	19"	
Reversible Front Locking Door	Smoked Acrylic	Smoked Acrylic	
Vented Side Panels	Fixed	Fixed	
Hinged Swing Out Design	Yes	Yes	
Reinforced Door Frame	Yes	Yes	
Front Cage Rails	Yes	Yes	
Single Key Lock Set	2 keys per set	2 keys per set	
Cable Access	Top:Cutouts	Top:Cutouts	
	Bottom:Cutouts	Bottom:Cutouts	
Electrostatic Powdercoat MicroFinish	Black & Ivory	Black & Ivory	
Preinstalled 80CFM 110V Fans	1	1	
Cage Nuts, Screws & Washers	12 Each	12 Each	
Compliance	EIA-310D	EIA-310D	
Delivery Style	Assembled	Assembled	

SECTION

02



300 Structure and Fabrication

Item No.	Color	Rack Units (U)	Structure (AWG)	Side Panels (AWG)	Top Panel (AWG)	Base (AWG)
WM3019-05-01	Ivory	5U	18	18	18	18
WM3019-05-02	Black	5U	18	18	18	18
WM3019-07-01	Ivory	7U	18	18	18	18
WM3019-07-02	Black	7U	18	18	18	18
WM3019-09-01	Ivory	9U	18	18	18	18
WM3019-09-02	Black	9U	18	18	18	18
WM3019-11-01	Ivory	11U	18	18	18	18
WM3019-11-02	Black	11U	18	18	18	18
WM3019-14-01	Ivory	14U	18	18	18	18
WM3019-14-02	Black	14U	18	18	18	18
WM3019-16-01	Ivory	16U	18	18	18	18
WM3019-16-02	Black	16U	18	18	18	18
WM 3019-20-02	Black	20U	18	18	18	18
WM 3019-28-02	Black	28U	18	18	18	18

WALL MOUNT ENCLOSURES

300 SERIES

SWING-OUT W/FIXED SIDE PANELS



300 Swing-Out Design Series

Item No.	Rack Units (1U=1.75") 19" Format	External Dimensions (inch)			Internal Dimensions (inch)			Load Capacity (lbs.)	Shipping Weight (Assembled)	Shipping Weight (Knockdown)
		H	W	D	H	W	D'			
WM3019-07-01 WM3019-07-02	7U	15	20.5"	23.5"	12.5"	19"	17"	130	46	N/A
WM3019-09-01 WM3019-09-02	9U	18.5	20.5"	23.5"	16"	19"	17"	130	51	N/A
WM3019-11-01 WM3019-11-02	11U	22"	20.5"	23.5"	19.5"	19"	17"	130	56	N/A
WM3019-14-01 WM3019-14-02	14U	27"	20.5"	23.5"	24.5"	19"	17"	130	59	N/A
WM3019-16-01 WM3019-16-02	16U	30.5"	20.5"	23.5"	28"	19"	17"	130	67	N/A
WM3019-20-02	20U	37.5"	20.5"	30.5"	35"	19"	24"	130	83	N/A
WM3019-28-02	28U	51.5"	20.5"	30.5"	49"	19"	24"	130	115	N/A

SECTION 02

NEW

1 - Internal dimensions measure from front rails to back door. All Wall Mount Enclosures have an additional 2" of usable space from rails to front door and all 300 Series Wall Mount Enclosures have an additional 3" of usable space in the hinged rear door.

300 Reversible Locking Front Door



Front locking door is reversible for left or right side opening.

300 Vented Fixed Side Panels



Vented fixed side panels for better air flow and equipment cooling.



300 Adjustable Cage Nut Rails



Includes adjustable cage nut rails and cage nuts with standard #12-24 mounting screws. All cage nut rails are marked with an RU space index for easy alignment when mounting equipment.

300 Swing-Out Locking Design



Swing-Out feature allows easy access to back of equipment with key lock to prevent tampering.

300 Pre-Installed Cooling Fans



Pre-Installed 110VAC 80CFM fan units keep equipment running cool.

300 Ships Fully Assembled



All 5U to 11U sizes are UPS shippable and ready for out-of-the-box installation.