

ROFU [®] STRIKES	Faceplate Size	Frame Jamb Type			Mortise Lock	Cylindrical Lock	Reversible Hand?	Max. Latch Proj.		Fail Safe	Fail Secure
		Wood	Alum.	Metal				5/8"	3/4"		
Standard Duty 1500 Series, 1000 lb. Tamper Resistance											
1501	1 1/4" x 5 7/8"	•			•	•	Y		✓		✓
1505	1 1/4" x 5 7/8"	•			•	•	Y		✓		✓
1507	1 1/8" x 2 3/4"		•	•	•	•	Y		✓		✓
1508	1 1/8" x 5 7/8"	•	•	•	•	•	Y		✓		✓
1509	1 7/16" x 7 15/16"	•	•	•	•	•	Y		✓		✓
1512	Rim Narrow	•	•	•	•	•	Y		✓		✓
Standard Duty 1400 Series, 1400 lbs. Tamper Resistance											
1401	1 1/4" x 5 7/8"	•			•	•	Y		✓		✓
1402	1 1/4" x 4 7/8"		•	•	•	•	Y		✓		✓
1402 RADIUS	1 1/4" x 4 7/8"		•		•	•	Y		✓		✓
1403	1 1/4" x 6 7/8"		•	•	•	•	Y		✓		✓
1403 RADIUS	1 1/4" x 6 7/8"		•		•	•	Y		✓		✓
1404	1 7/16" x 7 15/16"	•	•	•	•	•	Y		✓		✓
High Security 1400 Series, 1700 lbs. Tamper Resistance											
1430 (LH or RH)	1 1/4" x 4 7/8"		•	•	•	•	N		✓		✓
1440 (LH or RH)	1 1/4" x 4 7/8"		•	•	•	•	N		✓		✓
1450	1 1/4" x 4 7/8"		•	•	•	•	Y		✓		✓
1460	1 3/8" x 9"	•	•	•	•	•	Y		✓		✓
1460B (LH or RH)	1 3/8" x 9"	•	•	•	•	•	N		✓		✓
1470	1 3/8" x 9"	•	•	•	•	•	Y		✓		✓
1470B (LH or RH)	1 3/8" x 9"	•	•	•	•	•	N		✓		✓
Standard Duty 1700 & 1800 Series, 1000 lbs. Tamper Resistance, Adjustable Keeper											
1701	1 1/4" x 5 7/8"	•			•	•	Y	✓			✓
1702	1 1/4" x 4 7/8"	•	•	•	•	•	Y	✓			✓
1702 RADIUS	1 1/4" x 4 7/8"		•			•	Y	✓			✓
1703	1 1/4" x 6 7/8"	•	•	•	•	•	Y	✓			✓
1703 RADIUS	1 1/4" x 6 7/8"		•			•	Y	✓			✓
1704	1 7/16" x 7 15/16"	•	•	•	•	•	Y	✓			✓
1802	1 1/4" x 4 7/8"	•	•	•	•	•	Y	✓			✓
1803	1 1/4" x 6 7/8"	•	•	•	•	•	Y	✓			✓
1804	1 7/16" x 7 15/16"	•	•	•	•	•	Y	✓			✓
High Security 2400 Series, 1500 lbs. Tamper Resistance											
2400 - kit											
2402	1 1/4" x 4 7/8"	•	•	•	•	•	Y	✓		✓	✓
2404	1 7/16" x 7 15/16"	•	•	•	•	•	Y	✓		✓	✓
Standard Duty 3400 Series, 1400 lbs. Tamper Resistance (FAIL SAFE)											
3401	1 1/4" x 5 7/8"	•			•	•	Y		✓	✓	
3402	1 1/4" x 4 7/8"		•	•	•	•	Y		✓	✓	
3402 RADIUS	1 1/4" x 4 7/8"		•		•	•	Y		✓	✓	
3403	1 1/4" x 6 7/8"		•	•	•	•	Y		✓	✓	
3403 RADIUS	1 1/4" x 6 7/8"		•		•	•	Y		✓	✓	
3404	1 7/16" x 7 15/16"	•	•	•	•	•	Y		✓	✓	
High Security 3400 Series, 1700 lbs. Tamper Resistance (FAIL SAFE)											
3430 (LH or RH)	1 1/4" x 4 7/8"		•	•	•	•	N		✓	✓	
3440 (LH or RH)	1 1/4" x 4 7/8"		•	•	•	•	N		✓	✓	
3450	1 1/4" x 4 7/8"		•	•	•	•	Y		✓	✓	
3460	1 3/8" x 9"	•	•	•	•	•	Y		✓	✓	
3460B (LH or RH)	1 3/8" x 9"	•	•	•	•	•	N		✓	✓	
3470	1 3/8" x 9"	•	•	•	•	•	Y		✓	✓	
3470B (LH or RH)	1 3/8" x 9"	•	•	•	•	•	N		✓	✓	
Rim Mount, Exit Device 1960 Fail Secure 3960 Fail Safe, 1700 lbs. Tamper Resistance											
1960	1 3/4" x 9 7/16"	•	•	•		Exit Device			✓	✓	
3960	1 3/4" x 9 7/16"	•	•	•		Exit Device			✓		✓



ROFU® ELECTRIC STRIKE MODEL 1402/3402

1402 AND 3402 - SERIES, WITH ANSI FACEPLATE 1 1/4" x 4 7/8"

MODEL 1402 — Fail - Secure (Non Fail - Safe)

MODEL 3402 — Fail - Safe

Electric strikes for use with mortise and cylindrical locksets.

For Commercial and Residential, New or Retrofit Uses

Standard Features



1402/3402
Non-Handed

- Anodized Aluminum ANSI size Faceplate
- Frame Type - Hollow Metal or Aluminum
- Corrosion - Resistant case and moving parts.
- Tamper Strength Test - 1400 lbs (635kg)
- Cycle Test 500,000 cycles
- Keeper Depth - **5/8"** Maximum Latch Projection possible with 1/8" Door/Frame Clearance - **3/4"**
- Strike Depth 1.50" Overall
- Reversible - Non Handed
- Limited Warranty - **36 Months**

Available in the following Voltages and Finishes:

Specify Finish xUS28, xUS10B or xUS4

Voltage, Fail Secure x01=8-16VAC/3-6VDC, x05=12VAC/12VDC, x08=24VAC/24VDC

Voltage, Fail Safe x06=12VDC, x09=24VDC

Optional Features:



- Adjustable Keeper (FAFIX), available for 3402 series. Specify FAFIX
- Radius Faceplate for Aluminum Jamb, Specify "RAD." See drawing page #46
- 2" Lip Extension, specify #10002. See page #108






LINE ART FOR 1402/3402

HOLLOW METAL JAMB PREPARATION
FOR ALUMINUM JAMB SEE PAGE 45
FOR RADIUS ALUMINUM JAMB SEE PAGE 46



INSTALLATION



The mounting screws of the electric strike and the mounting screws of the deadlatch are located on the vertical centerline.

NOT TO SCALE - TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE